

Eaton E50DR19

Catalog Number: E50DR19

Eaton E50 NEMA heavy duty plug-in limit switch, Side rotary low temperature spring return, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, -40° to 175°F, E50 Heavy Duty Plug In

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50DR19 switch	UPC 782113328508

Product Length/Depth	Product Height
1.05 in	2.46 in

Product Width	Product Weight
1.54 in	0.11 lb

Warranty	Compliances
1 year	RoHS Compliant

Certifications
CSA Certified
UL Recognized

defaultTaxonomyAttributeLabel

Enclosure material

Die cast zinc

Actuator

Side rotary low temperature spring return

Series

E50 heavy duty plug in

Operating temperature - max

175 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50DR19](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)