

Eaton EBMX1B-W

Catalog Number: EBMX1B-W

Eaton Crouse-Hinds series clamped EBMXB circuit breaker enclosure, 15A through 100A, Without circuit breaker, Copper-free aluminum, Size 1 enclosure



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series clamped EBMXB circuit breaker enclosure	EBMX1B-W
	UPC
	662276606074
Product Length/Depth	Product Height
15.98 in	22.11 in
Product Width	Product Weight
12.86 in	80 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3R

4X

7

9

Product specifications

Enclosure cover construction

Clamped

Enclosure size

Size 1

Enclosure

Without circuit breaker

Manufacturer

Eaton

Amperage Rating

15A through 100A

Enclosure material

Copper-free aluminum

Resources

3D models

[SP3D Design Package - Clamped EBMXB Explosionproof Circuit Breakers](#)

Brochures

[EBMX Replacement Parts List](#)

[Clamped EBMX Series Explosionproof Combination Motor Starters Brochure](#)

Catalogs

[Clamped EBMXB Series Explosionproof Circuit Breakers catalog page](#)

Certification reports

[Clamped EBMXB Explosionproof Circuit Breakers UL certification](#)

[Clamped EBMXB Explosionproof Circuit Breakers Canadian certification](#)

Installation instructions

[IF 1794 - Clamped EBMX Motor Control Series](#)

[IF 1616 - Flange Gasket Replacement Kit](#)

[IF 1149 - Wiring](#)

Specifications and datasheets

[Eaton Specification Sheet - EBMX1B-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)