



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ESGS40 #2-4/0 Awg In-Line Gel Splice Kit (W/Connector)

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | ESGS40  |
| Manufacturer     | Nsi Industries  |
| Description      | Splice Kit, Copper/Aluminum Conductor Material, Black Insulation Color, -40 °F Operating Temperature, +194 °F Operating Temperature, 4.229 In Overall Length, 1000 V, 0.26 LB |
| Weight per unit  | 0.2600 (lbs/each)   |
| Product Category | Splicing & Terminating Kits   |

### Features

|                |           |
|----------------|-----------|
| Cable Size     | 2-4/0 AWG |
| Cable Type     | Class A-B |
| Voltage Rating | 1000 V    |
| Warranty       | 1 YEAR    |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | #2-4/0 AWG IN-LINE GEL SPLICE KIT (W/CONNECTOR)                           |
| extra long description | NSI ESGS-4/0 Easy-Splice Gel Tap 2/                                       |
| Special Features       | Provides Sealed Splice For Underground, Buried, And Overhead Applications |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00662381168610 |
| UPC  | 662381168610   |

### Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | SPLICE KITS            |
| Type                 | In-Line Gel Splice Kit |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 3    |
| Weight Per each | 0.26 |

### Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Splicing Wire                               |
| Operating Temperature standard | -40 C To 90 C<br>ANSI C119.1-1986 Qualified |