

FIBERGLASS

300 lbs. **TYPE IA**
load capacity*
*includes weight of worker and tools

STEPLADDER FS1500 SERIES



- Da Boot™ Patent #7,000,731 B2
- Molded Top with Tool Slots
- Inside spreader braces
- Double-rivet step construction
- Wide Back Braces
- Full channel fiberglass rail



ANSI
Meets or exceeds requirements of American National Standards Institute
ANSI A14.5



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS1502*	2'	3"	17"	18 1/4"	8	2.07'
FS1503	3'	3"	18 7/8"	28"	12	3.18'
FS1504	4'	3"	199/16"	2815/16"	14	3.18'
FS1505	5'	3"	211/16"	34 7/8"	17	4.27'
FS1506	6'	3"	229/16"	40 7/8"	20	5.49'
FS1508	8'	3"	259/16"	52 3/4"	26	8.29'
FS1510	10'	3"	289/16"	6411/16"	34	11.67'
FS1512	12'	3"	319/16"	76 1/16"	47	15.49'

*FS1502 is a folding step stand and is not equipped with Da Boot™

FIBERGLASS

250 lbs. **TYPE I**
load capacity*
*includes weight of user and tools

STEPLADDER FS2000 SERIES



- Slip resistant rubber feet
- Molded Top with Handyman's Tool Slots
- Pinch resistant spreader braces
- Double-rivet step construction
- Optional Molded Pail Shelf



ANSI
Meets or exceeds requirements of American National Standards Institute
ANSI A14.5



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS2004	4'	3"	18 13/16"	28 3/16"	12	3.18'
FS2005	5'	3"	20 5/16"	34 1/8"	15	4.27'
FS2006	6'	3"	21 13/16"	40"	17	5.49'
FS2008	8'	3"	24 13/16"	51 7/8"	22	8.29'

FIBERGLASS

225 lbs. **TYPE II**
load capacity*
*includes weight of user and tools

STEPLADDER FS4000 SERIES



- Molded Top with Tool Slots
- Slip resistant Feet
- Pinch resistant spreader braces
- Fiberglass rails



ANSI
Meets or exceeds requirements of American National Standards Institute
ANSI A14.5



MODEL	SIZE	BASE WIDTH	SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS4004	4'	18 3/16"	283/16"	11	2.7'
FS4006	6'	21 13/16"	401/16"	16	4.4'
FS4007	7'	23 5/16"	46"	18	5.3'
FS4008	8'	24 13/16"	51 7/8"	21	6.2'