



**Performance Overview:**

Wattage: 45 Watts  
 Lumen Output: Up to 5,300 Lumens  
 Efficacy (lm/W): Up to 118 Lumens  
 Kelvin: 4000K, 5000K  
 CRI: >80



Project: \_\_\_\_\_ Date: \_\_\_\_\_  
 Catalog #: \_\_\_\_\_  
 Notes: \_\_\_\_\_



**Ordering Guide:**

<b>ESL</b>	<b>WP</b>	<b>45W</b>	<b>2</b>		<b>Options &amp; Accessories</b>
ESL	TYPE	WATTS	GENERATION	KELVIN	EMERGENCY
	WP (WallPack)	45W	2 (2nd Generation)	40 (4000 Kelvin) 50 (5000 Kelvin)	Blank (No EMG) EMG (See Below)
					ESL-WP-PC (Photocell for 30W-135W Wall Packs)
					ESL-4OCC-LDD (Occupancy Sensor, 0-10v Dimming, 8'-20' Mounting)
					ESL-REM-100 (Remote control to field program 4OCC Sensor)
					ESL-EMG-2DC-9W (External Emergency Backup)

ITEM#	WATTS	LUMEN OUTPUT	EFFICACY (lm/W)	KELVIN	DLC QPL CODE
ESL-WP-45W-240	45W	5,223	117	4000K	PSWJ7MH8
ESL-WP-45W-250	45W	5,300	118	5000K	PJYJZVQM

†Not All Part Numbers DLC Qualified. For a Complete Listing Please Consult the DLC Qualified Products List (QPL).

### Product Specifications:

#### Optical:

- Precision Engineered Optical Lens
- Consistent Uniformity
- Impact Resistant
- UV Protection

#### Construction:

- Die Cast Aluminum Housing
- High Performance Heat Sink
- Weathertight LED Driver Housing
- Continuous Gasket Seal
- LEDs Mounted to and Protected by Aluminum Housing with Easy Driver Access Hinged Door
- (3) 1/2" Threaded Conduit Holes

### Electrical:

Wattage: 45 Watts

Power Factor: @120V: 0.91 / @277V: 0.9

Input Voltage: 120-277 VAC

Input Current @ 120V: 0.375 Amps

Input Current @ 277V: 0.162 Amps

Total Harmonic Distortion (THD):

THD @ 120V: 15%

THD @ 277V: 15%

Operating Temperature: -40°F to 104°F (-40°C to 40°C)

Lifespan: 50K Hours

Weight: 8.04 Lbs

### Options & Accessories:



#### ESL-4OCC-LDD

Sensor Type: Microwave

Sensitivity Adjustment: 20% / 50% / 75% / 100%

Dimming Control Output: 0-10V

Detection Radius/angle: Max. 26ft/360°

Detection Area (square footage): 2123ft<sup>2</sup>@20ft/360°

Mounting Height: 20ft Max

Remote Range: 50ft

Programming: Via Dip Switch

For more information please see the ESL-4OCC-LDD cut sheet



#### ESL-EMG-2DC-9W

Output Power: 9 Watts

Rated Voltage: 100-277 VAC, 50-60Hz

Emergency Operation: ≥90 Minutes

Charging Time: 24 Hours

2-Wire Illumination Test Switch

High Temperature, Nickel-Cadmium Battery

RoHS Compliant

UL 924, CSA C.22.2 No. 141-15, CEC Title 20

For more information please see the ESL-4OCC-LDD cut sheet



#### ESL-REM-100



#### ESL-WP-PC