

GAR2026, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR2026](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3" Pipe, 3"-3-1/2" Rod, Bright Dipped.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Catalog Number	GAR2026
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	267
UPC	781810236406
UPC 12 Digit	7818102364066

Dimensions

Dimension - B Length inch	3.50 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.62 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Width fraction	4-3/4 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3 IPS IPS
Conductor - Copper Tube Std Size Range	3 IPS IPS
Conductor - Pipe or Round Tube Size	3 in
Conductor - Rod Size	3 - 3.5 in
Conductor - Rod Size Range	3 in-3 1/2 in
Conductor Type	CU C Solid-Size CU C Str-Size CU Tube Std-Size Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - GAR2026_MODEL-PDF](#)

[3D Models - GAR2026_MODEL-IGES](#)

[3D Models - GAR2026_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)

[Sales Drawings - SD..015789-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-GAR2026-SPEC-EN | REV 6/2024

GAR2026, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR2026](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 4 AWG (Sol)-2/0 AWG (Str), 3" Pipe, 3"-3-1/2" Rod, Bright Dipped.



Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Catalog Number	GAR2026
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	267
UPC	781810236406
UPC 12 Digit	7818102364066

Dimensions

Dimension - B Length inch	3.50 in
Dimension - Height fraction	5-5/8 in
Dimension - Height inch	5.62 in
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.56 in
Dimension - Outside Diameter inch	3.50 in
Dimension - Width fraction	4-3/4 in
Dimension - Width inch	4.81 in
Dimension - Width mm	122 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	3 IPS IPS
Conductor - Copper Tube Std Size Range	3 IPS IPS
Conductor - Pipe or Round Tube Size	3 in
Conductor - Rod Size	3 - 3.5 in
Conductor - Rod Size Range	3 in-3 1/2 in
Conductor Type	CU C Solid-Size CU C Str-Size CU Tube Std-Size Rod-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - GAR2026_MODEL-PDF](#)

[3D Models - GAR2026_MODEL-IGES](#)

[3D Models - GAR2026_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical](#)

[Grounding](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)

[Sales Drawings - SD..015789-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-GAR2026-SPEC-EN | REV 6/2024