




GE
Lighting

66471 - F28T8/XL/SPP35/ECO

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



GENERAL CHARACTERISTICS

| | |
|-----------------------------------|--------------------------------|
| Lamp Type | Linear Fluorescent - Straight |
| | Linear |
| Bulb | T8 |
| Base | Medium Bi-Pin (G13) |
| Rated Life (NOM) | 40000.0 h |
| Rated Life (instant start) @ Time | 20000 h @ 3 h |
| | 28000 h @ 12 h |
| Rated Life (rapid start) @ Time | 40000.0 @ 3.0/45000.0 @ 12.0 h |
| Bulb Material | Sodalime glass |
| Starting Temperature (MIN) | 15.0 °C |
| Mercury Content (NOM) | 2.95 mg |
| Picograms of Mercury (NOM) | 30.22541 pg |
| Primary Application | Energy Saving |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 2600.0 |
| Mean Lumens (NOM) | 2440.0 |
| Nominal Initial Lumens per Watt (NOM) | 92.85714 |
| Color Temperature (NOM) | 3500.0 K |
| Color Rendering Index (CRI) (NOM) | 80.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|------|
| Wattage (NOM) | 28.0 |
|---------------|------|

DIMENSIONS

| | |
|------------------------------------|----------------------|
| Maximum Overall Length (MOL) (NOM) | 48.000 in(1219.2 mm) |
| Nominal Length (NOM) | 48.000 in(1219.2 mm) |
| Bulb Diameter (DIA) (NOM) | 1.000 in(25.4 mm) |

PRODUCT INFORMATION

| | |
|----------------------------|--------------------|
| Product Code | 66471 |
| Description | F28T8/XL/SPP35/ECO |
| Standard Package | Case |
| Standard Package GTIN | 10043168664711 |
| Standard Package Quantity | 36 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| UPC | 043168664714 |




GE
Lighting

66471 - F28T8/XL/SPP35/ECO

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



GENERAL CHARACTERISTICS

| | |
|-----------------------------------|--------------------------------|
| Lamp Type | Linear Fluorescent - Straight |
| | Linear |
| Bulb | T8 |
| Base | Medium Bi-Pin (G13) |
| Rated Life (NOM) | 40000.0 h |
| Rated Life (instant start) @ Time | 20000 h @ 3 h |
| | 28000 h @ 12 h |
| Rated Life (rapid start) @ Time | 40000.0 @ 3.0/45000.0 @ 12.0 h |
| Bulb Material | Sodalime glass |
| Starting Temperature (MIN) | 15.0 °C |
| Mercury Content (NOM) | 2.95 mg |
| Picograms of Mercury (NOM) | 30.22541 pg |
| Primary Application | Energy Saving |

PHOTOMETRIC CHARACTERISTICS

| | |
|---------------------------------------|----------|
| Initial Lumens (NOM) | 2600.0 |
| Mean Lumens (NOM) | 2440.0 |
| Nominal Initial Lumens per Watt (NOM) | 92.85714 |
| Color Temperature (NOM) | 3500.0 K |
| Color Rendering Index (CRI) (NOM) | 80.0 |

ELECTRICAL CHARACTERISTICS

| | |
|---------------|------|
| Wattage (NOM) | 28.0 |
|---------------|------|

DIMENSIONS

| | |
|------------------------------------|----------------------|
| Maximum Overall Length (MOL) (NOM) | 48.000 in(1219.2 mm) |
| Nominal Length (NOM) | 48.000 in(1219.2 mm) |
| Bulb Diameter (DIA) (NOM) | 1.000 in(25.4 mm) |

PRODUCT INFORMATION

| | |
|----------------------------|--------------------|
| Product Code | 66471 |
| Description | F28T8/XL/SPP35/ECO |
| Standard Package | Case |
| Standard Package GTIN | 10043168664711 |
| Standard Package Quantity | 36 |
| Sales Unit | Unit |
| No Of Items Per Sales Unit | 1 |
| UPC | 043168664714 |