




GE  
Lighting

**63543 - F32T8/735/PRO/EC**  
F32T8/735/PRO/EC



### GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	20000.0 h
Rated Life (rapid start) @ Time	15000 h @ 3 h
Bulb Material	20000.0 @ 3.0 h
Starting Temperature (MIN)	Sodalime glass
Mercury Content (NOM)	10.0 °C
Picograms of Mercury (NOM)	2.95 mg
Primary Application	60.35188 pg
	Full Wattage

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2450.0
Mean Lumens (NOM)	2300.0
Nominal Initial Lumens per Watt (NOM)	77.0
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	78.0

### ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

### DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

### PRODUCT INFORMATION

Product Code	63543
Description	F32T8/735/PRO/EC
Standard Package	00-Case
Standard Package GTIN	10043168635438
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168635431