



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2413 LKG Conn, 20A 125/250V, L14-20R, B/W *Hubbell Wiring Devices*

Catalog Number	HBL2413
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 125/250V Ac, 3-Pole 4-Wire Grounding, Nema L14-20R, Screw Terminal, Black and White Nylon.
Weight per unit	0.3500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
connection	Screw Terminals
Current Rating	20
insulation	Insulated Body
Material	Nylon
Number of Conductors	4
pallet quantity	2880
Poles	3-Pole
Voltage Rating	125/250

Material, Color, and Finish

Color	Black;White
-------	-------------

Dimensions and Weight

Size	2.33 in x 2.33 in x 3.86 in
------	-----------------------------

Descriptions

Description	LKG CONN, 20A 125/250V, L14-20R, B/W
extra long description	HWDK HBL2413 LKG CONN, 20A 125/250V
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA L14-20R, Screw Terminal, Black and White Nylon.
Product Type	LKG Conn, 20A 125/250V, L14-20R, B/W
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585038155
Manufacturers Part Number	HBL2413
UPC	783585038155

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	I14-20R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498