



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5379C FLG-RCPT, 20A 125V, 5-20P, SS *Hubbell Wiring Devices*

Catalog Number	HBL5379C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	2,500
Wire Size	#18 to #12

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	1.71 in x 1.69 in x 1.71 in
------	-----------------------------

Descriptions

Description	FLG-RCPT, 20A 125V, 5-20P, SS
extra long description	HWDK HBL5379C FLG-RCPT, 20A 125V, 5
Long Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Product Type	FLG-RCPT, 20A 125V, 5-20P, SS
Special Features	Impact resistant thermoplastic construction

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585174457
Manufacturers Part Number	HBL5379C
series	Extra Heavy Duty
UPC	783585174457



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Flanged Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42; NEMA® WD-6 Compliant; UL Listed, File E2186
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact