DESCRIPTION

The HBL series is ideal for high mounting height industrial or retail applications. Advanced optical designs provide maximum performance from either T5 or T8 lamps. Optional uplight component produces excellent ceiling uniformity. HBL's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to HID. Benefits include exceptional color rendering, high system efficacy, 95% lumen maintenance, long lamp life, instant on/instant re-strike, economical dimming, and uniform brightness control. Typical HBL applications include retail, shopping malls, light industrial and recreational environments.

SPECIFICATION FEATURES

Construction

Channel and end plates are constructed of die-formed steel. The channel provides strength, numerous KOs for easy installation, and excellent thermal dissipation without any special or proprietary components. Stiffening brackets add additional strength and rigidity to channel and reflectors.

Electrical

The HBL comes with a standard Class "P" electronic ballast and twist-lock lampholders. UL/ cUL listed for high ambient environments up to 55°C (131°F) for all lamp and ballast combinations listed. Suitable for damp locations.

Finish


Electrostatically applied baked white enamel finish is preceded by a multistage cleaning cycle, iron phosphate coating with rust inhibitor.

Optics

Die-formed, segmented optical design optimizes performance across three distributions. Optical choices include a narrow distribution for aisles, medium distribution for assembly and loading areas, or wide distribution for general, open area lighting. An uplight option is offered to permit ceiling uniformity and allow for ample lamp and luminaire heat dissipation.

Mounting

The HBL series is ideally suited for suspension mounting with optional wire hook and chain set, or cable mounting. Single monopoint mounting is also available with SPM tong hanger. Includes V Hangers for rapid installation.




Warranty


When operated in high ambient conditions, the HBL is supported by a 5 yr/55°C and 3 yr/65°C ballast warranty for T5 and T8 (277V) options when used w/ high temperature ballast in open, uplight configurations. To maximize your warranty, the HBL should be ordered with a hightemperature ballast in ambient environments that typically exceed 40°C (102°F).

Compliance


Options to meet Buy American and other domestic preference requirements



LAMP CONFIGURATIONS



DIMENSION TOP VIEW



HBL SERIES

Metalux

4 OR 6 T5 LAMPS

High-Bay Industrial Open Luminaire





ENERGY DATA

Input Watts: ER Ballast 454 = 229654 = 346

Luminaire Efficacy Rating LER = 71 (White) LER = 74 (Specular Inserts) Catalog Number: HBL-654T5-UPL

Yearly Cost of 1000 lumens, 3000 hrs at .08 KWH = \$3.24

*Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements

**Consult Pre Sales Technical Support.




igned to provide safe and conver





PHOTOMETRICS



HBL-654-N-UPL Candela Narrow Distribution (2) Electronic B

Narrow Distribution				
(2) Electronic Ballasts	Angle	Along II	45°	Across
(6) F54T5/841HO	0	10583	10583	10583
	5	10534	10535	10550
54WT5 lamps	10	10391	10306	10134
4400 lumens	15	10154	9792	9169
Spacing criterion:	20	9809	8931	7763
	25	9377	7773	6433
(II) 1.2 x mounting	30	8862	6554	5637
height, (⊥) 0.9 x	35	8262	5518	5199
mounting height	40	7587	4829	4855
Efficiency 97%	45	6853	4346	4597
Enciency 57 /8	50	6074	3919	4425
Test Report:	55	5252	3566	3973
HBL654NUPL.IES	60	4399	3265	3473
	65	3522	2754	2994
LER =74	70	2632	2260	2270
Yearly Cost of 1000	75	1755	1626	1571
lumens, 3000 hrs at	80	934	974	1066
.08 KWH = \$3.24	85	265	466	420
.00 KVVH = \$3.24	90	4	11	14

Coefficients of Utilization

rc	80%				70	%		50%				30%			10%		0%	
w	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
R																		
0	114	114	114	114	110	110	110	110	103	103	103	97	97	97	92	92	92	89
1	104	99	95	92	100	96	93	89	91	88	85	86	83	81	81	79	77	75
2	95	87	80	75	91	84	78	73	80	75	71	75	71	68	71	68	65	63
3	86	77	69	63	83	74	67	62	70	64	60	67	62	58	63	59	56	53
4	79	68	60	54	77	66	59	53	63	56	51	60	54	50	57	52	48	46
5	73	61	53	46	71	60	52	46	57	50	45	54	48	43	51	46	42	40
6	68	55	47	41	65	54	46	40	51	44	39	49	43	38	47	42	37	35
7	63	50	42	36	61	49	41	36	47	40	35	45	39	34	43	38	34	32
8	59	46	38	33	57	45	37	32	43	36	32	41	35	31	40	34	30	28
9	55	42	35	29	53	42	34	29	40	33	29	38	32	28	37	31	28	26
0	52	39	32	27	50	38	31	27	37	31	26	36	30	26	34	29	25	24

Zonal Lumen Summary

Luminance Data

Zone	Lumens	%Lamp	%Fixture	Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
0-30	7354	27.9	28.7	45	16466	10442	11045
0-40	11251	42.6	43.9	45	16466	10442	11045
0-60	18573	70.4	72.5				
0-90	23479	88.9	91.6	55	15557	10563	11768
				65	14159	11071	12036
0-180	25621	97.0	100.0	75	11520	10673	10312
				85	5166	9084	8187

Candela

HBL-654-W-UPL

Wide Distribution

(2) Electronic Ballasts	Angle	Along II	45°	Across⊥
(6) F54T5/841HO	0	6850	6850	6850
	5	6814	6836	6863
54WT5 lamps	10	6739	6770	6796
4400 lumens	15	6607	6648	6668
Spacing criterion:	20	6418	6461	6487
1 0	25	6179	6222	6278
(II) 1.3 x mounting	30	5891	5945	6049
height, (⊥) 1.3 x	35	5558	5637	5792
mounting height	40	5183	5301	5498
Efficiency 93.3%	45	4773	4929	5187
Efficiency 55.576	50	4335	4526	4827
Test Report:	55	3866	4100	4434
HBL654WUPL.IES	60	3370	3638	3997
150 34	65	2843	3159	3437
LER =71	70	2283	2630	2685
Yearly Cost of 1000	75	1672	1932	1941
lumens, 3000 hrs at	80	1012	1216	1267
	85	348	548	548
.08 KWH = \$3.38	90	4	37	50

Coefficients of Utilization

C		80	%			70	%			50%			30%			10%		0%
v	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
R																		
)	109	109	109	109	105	105	105	105	98	98	98	92	92	92	86	86	86	84
ī.	99	94	90	86	95	91	87	84	85	82	79	80	77	75	75	73	71	68
2	89	81	74	69	86	78	72	67	74	69	64	69	65	61	65	62	59	56
3	81	71	63	57	78	68	61	55	64	58	53	60	55	51	57	53	49	46
ŧ	74	62	54	47	71	60	53	47	57	50	45	53	48	43	50	46	42	39
5	68	55	47	40	65	54	46	40	51	44	38	48	42	37	45	40	36	34
5	62	50	41	35	60	48	40	34	46	39	33	43	37	32	41	35	31	29
7	58	45	37	31	55	44	36	30	41	34	29	39	33	29	37	32	28	26
3	54	41	33	27	52	40	32	27	38	31	26	36	30	25	34	29	25	23
9	50	37	30	24	48	36	29	24	35	28	23	33	27	23	31	26	22	20
5	47	34	27	22	45	34	26	22	32	26	21	30	25	21	29	24	20	18


Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture	Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
0-30	5401	20.5	21.9				
0-40	8947	33.9	36.3	45	11468	11843	12463
0-60	16453	62.3	66.8		44.454		10101
0-90	22065	83.6	89.6	55	11451	12144	13134
0-180	24626	93.3	100.0	65	11429	12699	13817
0-100	24020	55.5	100.0	75	10975	12682	12741
				85	6784	10682	10682

Luminance Data

Modular F-Bay Power Supply Option

Cooper Lighting's F-Bay Modular Power Supply option is available for use with all F-Bay products. The modular power supply allows external fixture access for safe and easy servicing. There is no need to remove lamps or reflectors to disconnect fixture power with F-Bay Modular Power Supply. Access to the individual fixture's power supply allows servicing without turning off all the fixtures, disrupting occupants. F-Bay Modular Power Supply is a time-saver in installation - simply plug & power.



- 1. Modular Power Supply Receptacle supplied mounted into fixture Access Plate
- 2. Modular Power Cord & Plugs in 120, 277, 347, & 480V configurations for easy plug & power into existing supply



No internal fixture access required for installation or disconnecting power



Modular Motion Sensor Option supplied with Mounting Box and Modular Power Supply Receptacle

Code Compliance

- UL/cUL Certified for Make/Break under load (UL2549)
- Meets NEC requirements for ballast disconnect (NEC 410.73G)
- Allows for addition of Occupancy Sensor without hard connections
- · Receptacles complete with insulating/dust cap




Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2024 Cooper Lighting Solutions All Rights Reserved.

Specifications and dimensions subject to change without notice.

ORDERING INFORMATION




NOTES: ⁽¹⁾Voltage must be specified when ordered with plugs or emergency ballasts. For MS option, indicate UNV (for 120V or 277V), 347V or 480V. ⁽²⁾EBT ballast systems suitable for operation in ambient environments up to 104°F (40°C) in uplight configuration. ⁽³⁾EHT/HT5/HCT5 ballast systems are suitable for ambient environments not to exceed 149°F (65°C) in uplight configurations. ⁽⁴⁾Requires use of MC_ or MPC_ cord accessories, specify voltage for plugs. ⁽⁶⁾CCannot be combined with Modular Power Receptacle (MP). ⁽⁶⁾Recommended when using motion sensor options or accessories. ⁽⁷⁾Can be used in high abuse applications such as gymnasiums. ⁽⁸⁾For MWS with MP, choose MP in fixture logic and then choose MWS accessory such as MDS6. ⁽⁶⁾Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. ⁽¹⁰⁾ Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative for availability and ordering information.



Quick Ship Ordering Information Sample Number: HBL454T5-MP-UPL Includes V Hangers for rapid installation⁽⁷⁾ Quick Ship orders ship in 5 days in order quantities not to exceed 200 pieces.

der NOTE: Orders received after noon are entered on the following day.



NOTES: ⁽⁸⁾ T5 ballast systems suitable for operation in ambient environments up to 104°F (40°C) in uplight configuration. ⁽⁹⁾EHT/HT5/HCT5 ballast systems are suitable for ambient environments not to exceed 149°F (65°C) in uplight configurations. ⁽¹⁰⁾ Requires use of MC_ or MPC_ cord accessories, specify voltage for plugs.

SHIPPING DATA

Catalog No. HBL-454T5-UNV-UPL HBL-654T5-UNV-UPL **Wt**. 13.5 lbs. 15 lbs.



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com © 2024 Cooper Lighting Solutions All Rights Reserved.

Specifications and dimensions subject to change without notice.

ADF081981 June 19, 2024 10:26 AM