



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL7506C LKG Conn, 15A 125V, L1-15R

Hubbell Wiring Devices

Catalog Number	HBL7506C
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 125V , 2-Pole 2-Wire Non-Grounding, Nema L1-15R, Screw Terminal, Black and White Nylon.
Weight per unit	0.1500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Pressure Screw Terminal
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	2
pallet quantity	3600
Poles	2-Pole
Voltage Rating	125

Material, Color, and Finish

Color	Black;White
-------	-------------

Dimensions and Weight

Size	1.53 in x 1.53 in x 2.78 in
------	-----------------------------

Descriptions

Description	LKG CONN, 15A 125V, L1-15R
extra long description	HWDK HBL7506C LKG CONN, 15A 125V, L
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 125V , 2-Pole 2-Wire Non-Grounding, NEMA L1-15R, Screw Terminal, Black and White Nylon.
Product Type	LKG Conn, 15A 125V, L1-15R
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585177908
Manufacturers Part Number	HBL7506C
UPC	783585177908

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L6-15R
standard	Certified to CSA C22.2 No. 42; Fed. Spec W-C-596; Listed to UL 498
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.