



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL8300HRED Dup RCPT, Com/HG, 20A 125V, 5-20R, RD *Hubbell Wiring Devices*

|                  |   |
|------------------|---|
| Catalog Number   | HBL8300HRED   |
| Manufacturer     | Hubbell Wiring Devices  |
| Description      | Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Red, Single Pack. |
| Weight per unit  | 0.0780 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                     |                                     |
|---------------------|-------------------------------------|
| amperage rating     | 20                                  |
| connection          | Back and Side Wired Screw Terminals |
| Current Rating      | 20                                  |
| Dielectric Strength | Withstands 2,000V minimum           |
| Material            | Nylon                               |
| Number of Wires     | 3-Wire                              |
| pallet quantity     | 3600                                |
| Phase               | 1                                   |
| Poles               | 2-Pole                              |
| Voltage Rating      | 125 V                               |
| Wattage             | 2500                                |
| Wire Size           | #12 to #10                          |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | 3.28 in x 1.33 in x 1.05 in |
|------|-----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | DUP RCPT, COM/HG, 20A 125V, 5-20R, RD  |
| extra long description | HWDK HBL8300HRED DUP RCPT, COM/HG,   |
| Features               | HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these |
| Long Description       | Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Red, Single Pack.  |
| Product Type           | Dup RCPT, Com/HG, 20A 125V, 5-20R, RD  |
| Special Features       | Standard Product   |

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585247519        |
| Manufacturers Part Number | HBL8300HRED           |
| series                    | Hospital Grade        |
| UPC                       | 783585247519          |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type                 | Duplex Receptacle      |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 10    |
| Weight Per each | 0.078 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Hospital grade  |
| environmental conditions | Indoor Dry unless protected by additional means   |
| Mounting                 | Screw Mount   |
| nema rating              | 5-20R   |
| standard                 | CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186 |