



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCTR25 25A 600V Class CC Time Delay Small Control Fuse

*Edison Fuses*

Catalog Number	HCTR25
Manufacturer	Edison Fuses
Description	Eaton Edison HCTR Fuse, Non-Indicating, 25 A, Class CC, 10 Kaic, Standard, 10, 600 V
Weight per unit	0.0010 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	25 A
class	Class CC
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
interrupt rating	10 kAIC
media	Yes
Voltage Rating	600 V

### Descriptions

Description	25A 600V CLASS CC TIME DELAY SMALL CONTROL FUSE
extra long description	EFSE HCTR25 UL CLASS CC TIME DELAY
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Long Description	Eaton Edison HCTR fuse, Non-indicating, 25 A, Class CC, 10 kAIC, Standard, 10, 600 V
Product Type	UI Class CC Time Delay
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00782634839002
Manufacturers Part Number	HCTR25
UPC	782634839002

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.001

## Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	UL Listed,CSA Certified,CE Marked,RoHS Compliant