



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HKD3300W HKD BRKR 3P 300A 600VAC Max 65KAIC @ 480V

Eaton Corp

Catalog Number	HKD3300W
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, K-Frame, HKD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 300A, 600 Vac, 250 VDC, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Without Terminals, 50/60 HZ
Weight per unit	11.5 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	300 A
dimensions	4.1000 IN X 5.5000 IN X 5.5000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	HKD BRKR 3P 300A 600VAC MAX 65KAIC @ 480V
extra long description	ETN HKD3300W HKD BRK 3P 300A 600VAC
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, K-frame, HKD, Complete breaker, Fixed thermal, fixed magnetic trip, Three-pole, 300A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Without terminals, 50/60 Hz
Product Type	HKD BRK 3P 300A 600VAC Max 65KAIC @ 480V

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679342909
Manufacturers Part Number	HKD3300W
UPC	786679342909

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	11.5

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed