



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLD3600 HLD 3P 600AMP L & L Term *Eaton Corp*

Catalog Number	HLD3600
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, L-Frame, HLD, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 600 A, 600 Vac, 250 VDC, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Aluminum, Line and Load, 50/60 HZ
Weight per unit	17.0 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	600 A
dimensions	8.2500 IN X 8.2500 IN X 8.2500 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	HLD 3P 600AMP L & L TERM
extra long description	ETN HLD3600 HLD 3P 600AMP L & L TER
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, L-frame, HLD, Fixed thermal, Fixed magnetic trip, Three-pole, 600 A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz
Product Type	HLD 3P 600AMP L & L Term

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679009611
Manufacturers Part Number	HLD3600
UPC	786679009611

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	17

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed