



## GHB2070 Type GHB BRKR 2P 70A 277/480VAC Max 125/250VDC Max

Eaton Corp

Catalog Number	GHB2070
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 70 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ
Weight per unit	1.2 (lbs/each)
Product Category	2 Pole

### Features

Current Rating	70A
Dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
Frame	G
Media	Yes
Poles	2
Voltage Rating	480Y/277 Vac, 125/250 Vdc

### Descriptions

Description	TYPE GHB BRKR 2P 70A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB2070 GHB CB 2P 70A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 70 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz
Product Type	GHB CB 2P 70A 277/480VAC Max 125/250VDC

### Manufacturer Information

Brand	Eaton
GTIN	00786679172520
Manufacturers Part Number	GHB2070
UPC	786679172520

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2700 Summit Ave. Suite 200  
75074-0000, TX Plano  
Phone: 469-467-7771  
Fax: 469-467-0282

## Packaging

Carton	1
Package	12
Weight Per each	1.15

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed, Federal Specifications Classification W-C375B