



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISPB3504 350MCM-12AWG 4PRT Ped Conn

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | ISPB3504  |
| Manufacturer     | Nsi Industries  |
| Description      | The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector Features 4 Ports Sized For 350 MCM - 12 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrenc |
| Weight per unit  | 0.7300 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                      |                |
|----------------------|----------------|
| Material             | Aluminum       |
| Number of Conductors | 4              |
| Poles                | 1              |
| Voltage Rating       | 600 V          |
| Warranty             | 1 YEAR         |
| Wire Size            | 350 MCM-12 AWG |
| Wire Type            | Class B & C    |

### Material, Color, and Finish

|        |                       |
|--------|-----------------------|
| Color  | Black                 |
| Finish | EPDM Rubber Insulated |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | L=4.800 - W=4.190 - H=3.060 |
|------|-----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 350MCM-12AWG 4PRT PED CONN   |
| extra long description | NSI ISPB350-4 POLARIS EDGE Connector   |
| Features               | The Polaris ISPB350-4 4-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to four conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in   |
| Long Description       | The Polaris ISPB350-4 Multi-Tap Direct Burial Single-Sided Entry Connector features 4 ports sized for 350 MCM - 12 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench |
| Product Type           | Polaris Edge Connector 350 4 Port BLK  |
| Special Features       | (4) 350 MCM-12 AWG - Dual Rated  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Polaris        |
| GTIN                      | 00662381788962 |
| Manufacturers Part Number | ISPB350-4      |
| UPC                       | 662381788962   |

## Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | TERMINALS                       |
| Type                 | Submersible Pedestal Connectors |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 2    |
| Weight Per each | 0.73 |

## Uses, Certifications, and Standards

|                          |                     |
|--------------------------|---------------------|
| Application              | Wire Termination    |
| environmental conditions | 90 C                |
| standard                 | ANSI C119.4, C119.1 |
| Temperature Rating       | 90 C                |