




KC22J12T13, Mechanical Transformer Connector, Fits standard EEI-NEMA distribution Transformers as Tank Grounding Terminal, #8 Sol-#2 Sol Copper

By Burndy
Catalog # [KC22J12T13](#)



Copper transformer ground connector. Fits all standard EEI-NEMA distribution transformers as tank grounding terminal, Accommodates: 8 Sol. - 2 Sol. Copper

General

Application	For Used To Fit All Standard EEI-NEMA Distribution Transformers As A Tank Grounding Terminal
Catalog Number	KC22J12T13
EU RoHS Indicator	Yes
Installation Torque	80 LBS/in
Recommended in-lb	
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	80 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810127872
UPC 12 Digit	7818101278722

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	1/2
Dimension - Cross Flats inch	0.62 in
Dimension - D inch	0.50 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - P inch	0.27 in
Dimension - Threads per inch	13
Dimension - Width inch	25 mm
Dimension - Width mm	22 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Conductor - Copper Str Size Range	3 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	17400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_kcjtla](#)
[Sales Drawings - SD..208818-01](#)




A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KC22J12T13-SPEC-EN | REV 6/2024



KC22J12T13, Mechanical Transformer Connector, Fits standard EEI-NEMA distribution Transformers as Tank Grounding Terminal, #8 Sol-#2 Sol Copper

By Burndy
Catalog # [KC22J12T13](#)



Copper transformer ground connector. Fits all standard EEI-NEMA distribution transformers as tank grounding terminal, Accommodates: 8 Sol. - 2 Sol. Copper

General

Application	For Used To Fit All Standard EEI-NEMA Distribution Transformers As A Tank Grounding Terminal
Catalog Number	KC22J12T13
EU RoHS Indicator	Yes
Installation Torque	80 LBS/in
Recommended in-lb	
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	80 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810127872
UPC 12 Digit	7818101278722

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	1/2
Dimension - Cross Flats inch	0.62 in
Dimension - D inch	0.50 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - P inch	0.27 in
Dimension - Threads per inch	13
Dimension - Width inch	25 mm
Dimension - Width mm	22 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Conductor - Copper Str Size Range	3 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	17400

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_kcjtla](#)
[Sales Drawings - SD..208818-01](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KC22J12T13-SPEC-EN | REV 6/2024