

Twist-Lock® Devices

20A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding

Single Flush Receptacle

HUBBELL

Features

- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|----------------------|--------------|--------------|----------------|
| Nylon face, back and | Black | 783585235752 | HBL2420 |

Listings

Listed to UL 498
Fed. Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------|--|
| Face | Nylon |
| Base | Glass-Reinforced thermoplastic polyester (RTP) |
| Contacts | Brass |
| Terminal Screws | #10 - 32 Brass |
| Mounting Strap | Brass |

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.


Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability V2 or better per UL94/CSA 22.2 No.0.17
Moisture Resistance IP20 Suitability
Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



20A 3Ø 250V AC
NEMA L15-20R
UL/CSA
3 HP



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Accessories

| | |
|---------------------------------|---------------|
| Plug | HBL2421 |
| Wallplate or Weatherproof Cover | 1.60" Opening |
| Switched Enclosure | SETL3 |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Twist-Lock® Devices

20A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding

Single Flush Receptacle

HUBBELL

Features

- Wire restraint recess for both back and side wiring, greatly reduces the possibility of loosening the terminal connection
- Face color coding by voltage facilitates locating and mating of proper devices
- All-brass mounting and grounding system provides a lower resistance ground path and greater resistance to corrosion than steel mounting systems

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|----------------------|--------------|--------------|----------------|
| Nylon face, back and | Black | 783585235752 | HBL2420 |

Listings

Listed to UL 498
Fed. Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

| | |
|-----------------|--|
| Face | Nylon |
| Base | Glass-Reinforced thermoplastic polyester (RTP) |
| Contacts | Brass |
| Terminal Screws | #10 - 32 Brass |
| Mounting Strap | Brass |

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.


Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability V2 or better per UL94/CSA 22.2 No.0.17
Moisture Resistance IP20 Suitability
Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



20A 3Ø 250V AC
NEMA L15-20R
UL/CSA
3 HP



Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Accessories

| | |
|---------------------------------|---------------|
| Plug | HBL2421 |
| Wallplate or Weatherproof Cover | 1.60" Opening |
| Switched Enclosure | SETL3 |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

