



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1420C Turnlok Conn 4W 20A 125/250V B&W

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | L1420C |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok® Connector 4-Wire 20A 125/250V |
| Weight per unit | 0.3780 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|---------|
| amperage rating | 20 |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage Rating | 125/250 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Black&White |
|-------|-------------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK CONN 4W 20A 125/250V B&W |
| extra long description | P&S L1420C TURNLOK CONNECTOR 4W 20A |
| Long Description | Turnlok® Connector 4-Wire 20A 125/250V |
| Product Type | Turnlok Connector 4W 20A 125/250V B&W |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007142013 |
| Manufacturers Part Number | L1420-C |
| UPC | 785007142013 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Turnlock Connector |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.378 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial Spec Grade |
| Mounting | Connector |
| nema rating | I14-20R |
| standard | UL 498 |