

INDUSTRIAL COMMERCIAL

E-39 **DEVICES**

TESTING & CODE COMPLIANCE

· Listed to UL 498 Receptacles: (file no. E15058); UL verified to Federal Spec. WC-596; Plugs & Connectors: (file no. E15012). · CSA Certified to C22.2 no. 42. Receptacles: (file no. LR6914 (6233-01)),Plugs & Connectors: (file no. LR2081 (6221-02)). · NOM Certified,

MATERIAL CHARACTERISTICS

except as noted.

Receptacles: Nylon. Plugs, Connectors: Polycarbonate. Meets flammability requirements per UL 94, V2 rated. Temperature Rating: Receptacles: -40°C to 70°C. Plugs & Connectors: -20°C to 60°C.





Commercial Specification Grade Locking Devices

3 Pole, 4 Wire Grounding NEMA L14-30, 30A 125/250V NEMA L15-30, 30A 250V 3Ø NEMA L16-30, 30A 480V 3Ø NEMA L17-30, 30A 600V 3Ø


30A 3 Pole, 4 Wire **Commercial Specification Grade Receptacles**

FEATURES

- Rugged nylon face and body.
- Clearly marked rating, NEMA configuration and approval listings on receptacle face.
- One piece brass contacts offer superior performance and minimum heat rise.
- Back wire terminal clamps for easy secure wiring.
- Combination head screws standard slot/Phillips in the U.S.

1.70" (43.2mm)3.28 2.39" (83.3mm) (60.7mm)2.38 (60.5mm) 1.15 (29.2mm)1.55" (39.4mm)

L1430R



(60.7mm)

L1630R

Commercial Specification Grade Receptacles Rating

Α	V/AC	NEMA	Description	Color	Catalog No.		
30	125/250	L14-30	Single	Black	L1430R		
30	250V 3Ø	L15-30	Single	Black	L1530R		
30	480V 3Ø	L16-30	Single	Black	L1630R*		
30	600V 3Ø	L17-30	Single	Black	L1730R*		

*Not NOM

30A 3 Pole, 4 Wire Commercial Specification Grade **Locking Plugs and Connectors**

FEATURES

- Abuse resistant thermoplastic construction.
- Back wire Dead-Front design.
- External cable clamp provides firm strain relief.
- Back wire terminal clamps for easy secure wiring.
- Individual wiring compartments with tapered channel for easy insertion of wires.
- Triple combination head screws standard slot/Phillips/Robertson for use in the U.S. and Canada.
- Clear cover over wiring compartments allow easy inspection of wiring terminations.
- Clearly marked rating, NEMA configuration and standard compliances on face of plug or connector.

2.00" (50.80mm) 2.75 (69.85mm)

L1430P

Commercial Specification Grade Locking Plugs and Connectors

Rating			Description/		Catalog No.	
Α	V/AC	NEMA	Cord Diameter	Color	Plug	Connector
30	125/250	L14-30	Straight: 0.25"-0.69" (6.35mm-17.5mm)	Black & White	L1430P	L1430C
30	250V 3Ø	L15-30	Straight: 0.25"-0.69" (6.35mm-17.5mm)	Black & White	L1530P	L1530C
30	480V 3Ø	L16-30	Straight: 0.25"-0.69" (6.35mm-17.5mm)	Black & White	L1630P	L1630C

NOTE: Weather Protective Covers from Cooper Wiring Devices that may be used with these products are described on pages E-71 in this section.











L16-30P





L14-30R L15-30P L14-30P

L15-30R

L16-30R

L17-30R

