



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2423 LKG Conn, 20A 3P 250V, L15-20R, B/W** *Hubbell Wiring Devices*

Catalog Number	HBL2423
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 3-Phase 250V Ac, 3-Pole 4-Wire Grounding, Nema L15-20R, Screw Terminal, Black and White Nylon.
Weight per unit	0.4500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	20
connection	Pressure Screw Terminal
Current Rating	20
insulation	Insulated Body
Material	Nylon
Number of Conductors	4
pallet quantity	3060
Poles	3-Pole
Voltage Rating	3 Phase 250

### **Material, Color, and Finish**

Color	Black;White
-------	-------------

### **Dimensions and Weight**

Size	2.33 in x 2.33 in x 3.86 in
------	-----------------------------

### **Descriptions**

Description	LKG CONN, 20A 3P 250V, L15-20R, B/W
extra long description	HWDK HBL2423 LKG CONN, 20A 3P 250V,
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 3-Phase 250V AC, 3-Pole 4-Wire Grounding, NEMA L15-20R, Screw Terminal, Black and White Nylon.
Product Type	LKG Conn, 20A 3P 250V, L15-20R, B/W
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585038216
Manufacturers Part Number	HBL2423
UPC	783585038216

### **Taxonomies, Classifications, and Categories**

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	30
Weight Per each	0.45

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L15-20R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498