



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2611 LKG Plug, 30A 125V, L5-30P, B/W *Hubbell Wiring Devices*

Catalog Number	HBL2611
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White.
Weight per unit	0.3000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
connection	Screwed Terminal
Cord Type	All Listed Portables
Current Rating	30
Material	Nylon
Number of Wires	3-Wire
pallet quantity	3060
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	3
Wire Size	#16 to #8

### Material, Color, and Finish

Color	BLACK, WHITE
-------	--------------

### Dimensions and Weight

Size	2.26 in x 2.26 in x 2.75 in
------	-----------------------------

### Descriptions

Description	LKG PLUG, 30A 125V, L5-30P, B/W
extra long description	HWDK HBL2611 LKG PLUG, 30A 125V, L5
Long Description	Locking Devices, Twist-Lock®, Industrial, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White.
Product Type	LKG Plug, 30A 125V, L5-30P, B/W
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585038735
Manufacturers Part Number	HBL2611
UPC	783585038735



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Plugs

## Packaging

Carton	1
Package	30
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L5-30P
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498