



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L520P Turnlok Plug 3W 20A 125V B&W

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | L520P |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Device Turnlock Plug, 20 A, 125 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 2.20 In;0.225 to 1.150 In (Cord) Diameter, Plug Mount, 3.75 In Length, #18 to #8 Awg Wire Size, Impact Resistant, Corrosion Resistant, 0.33 LB |
| Weight per unit | 0.3320 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|-----|
| amperage rating | 20 |
| Poles | 2 |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Black&White |
|-------|-------------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.8 in |
|------|--------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | TURNLOK PLUG 3W 20A 125V B&W |
| extra long description | P&S L520P TURNLOK PLUG 3W 20A 125V |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007252040 |
| Manufacturers Part Number | L520P |
| UPC | 785007252040 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Industrial cord connectors |
| Type | Turnlock Plug |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.332 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Mounting
standard

Plug
CULUS, UL 498