



GE  
Lighting

39350 - null

LED7DMRX1683025

#### GENERAL CHARACTERISTICS

Primary Application	Track & Recessed
Product Technology	LED
Rated Life (Hours)	25000 h
Base	GU5.3

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	25 deg
Center Beam Candle Pwr Candela	1900 cd
Nominal Initial Lumen per Watt	60
Rated Beam Spread	25 deg
Initial Lumens-nominal	420 lm
Color Rendering Index-CRI	82
Color Temperature	3000 K

#### PRODUCT INFORMATION

Product Code	39350
Description	LED7DMRX1683025
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168393508
Standard Package GTIN	00043168393508
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168393508
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168393508
Standard Package GTIN	10043168393505
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168393508

#### DIMENSIONS

Bulb Max Overall Length-MOL	2.2 in
-----------------------------	--------

#### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Input Voltage [nom]	12 V



GE  
Lighting

39350 - null

LED7DMRX1683025

#### GENERAL CHARACTERISTICS

Primary Application	Track & Recessed
Product Technology	LED
Rated Life (Hours)	25000 h
Base	GU5.3

#### PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	25 deg
Center Beam Candle Pwr Candela	1900 cd
Nominal Initial Lumen per Watt	60
Rated Beam Spread	25 deg
Initial Lumens-nominal	420 lm
Color Rendering Index-CRI	82
Color Temperature	3000 K

#### PRODUCT INFORMATION

Product Code	39350
Description	LED7DMRX1683025
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168393508
Standard Package GTIN	00043168393508
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168393508
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168393508
Standard Package GTIN	10043168393505
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168393508

#### DIMENSIONS

Bulb Max Overall Length-MOL	2.2 in
-----------------------------	--------

#### ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Input Voltage [nom]	12 V