



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBLDS10 Disconnect, 100A Unfused, 4X

Hubbell Wiring Devices

Catalog Number	HBLDS10
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 100A 600V Ac, Screw Terminals, Gray, Nema 4xenclosure
Weight per unit	5.6 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### Features

action	Snap
amperage rating	100
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	100A
Current Rating	100
Material	COMPOSITE
operating cycles	6,000
pallet quantity	140
Poles	3
Switch Type	Lever
Voltage Rating	600
Wattage	60000;60000.0000

### Dimensions and Weight

Size	11 in x 7.75 in x 5.94 in
------	---------------------------

### Descriptions

Description	DISCONNECT, 100A UNFUSED, 4X
extra long description	HWDK HBLDS10 DISCONNECT, 100A UNFUS
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motorand driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 100A 600V AC, Screw Terminals, Gray, NEMA 4XEnclosure
Product Type	Disconnect, 100A Unfused, 4X
Special Features	Standard Product



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585430652
Manufacturers Part Number	HBLDS10
series	Non-Fused
UPC	783585430652

## Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Disconnect Switches

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	5.55

## Uses, Certifications, and Standards

Application	Labelless
Enclosure	Type 4X, IP69k
environmental conditions	NEMA 4X
Mounting	Mounting Feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
standard	UL Listed