



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HM600303CR 30A 600V 3P Class H Fuse Block *Bussmann Fuses*

Catalog Number	HM600303CR
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series HM Modular Fuse Block, CR, 0-30 A, Three-Pole, Class H, Class K, 10 Ka, 10 Kaic, 600 V
Weight per unit	2.2 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	0-30A
class	Class KClass H
dimensions	6.2000 IN X 3.4800 IN X 2.2500 IN
media	Yes
Voltage Rating	600V

Descriptions

Description	30A 600V 3P CLASS H FUSE BLOCK
extra long description	BUSS HM60030-3CR Fuse Block, Class
Features	Eaton's Bussmann series power distribution fuse blocks (PDFB) combine a fuse block and power distribution block into one component. This patented design simplifies your panel layout and uses up to 57 less panel space. Additionally, it lowers inventory costs while reducing installation time and labor by 33. Bussmann series PDFBs are available for Class H(K) ferrule fuses. PDFBs up to 60 amps feature DIN-Rail and panel mount versatility for ease of installation.
Long Description	Eaton Bussmann series HM modular fuse block, CR, 0-30 A, Three-pole, Class H, Class K, 10 kA, 10 kAIC, 600 V
Product Type	Fuse Block, Class H, 600V 30A, 3 Pole
Special Features	CR

Manufacturer Information

Brand	Eaton
GTIN	00051712511476
Manufacturers Part Number	HM60030-3CR
UPC	051712511476

Taxonomies, Classifications, and Categories

Category Description	FUSE BLOCKS,FUSE HOLDERS
Type	Modular fuse block

Packaging

Carton	4
Weight Per each	2.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

Contact Manufacturer ,CSA Certified ,UL Listed,RoHS Compliant