



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT112 1-1/2" Met L/T, Non UI 50' *Southwire Company*

Catalog Number	LT112
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1-1/2 In Trade Size, 1.865 to 1.9 In Conduit Outer Diameter, 1.575 to 1.6 In Conduit Inner Diameter, Titan(R) Ef Style, 50 FT Length, Galvanized, Gray, 9 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 95 LB/100 FT
Weight per unit	0.8300 (lbs/ft)
Product Category	Liquid Tight Conduit

Features

outside diameter	1833
------------------	------

Descriptions

Description	1-1/2" MET L/T, NON UL 50'
extra long description	SWC 55107102 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043086
UPC	032886043086

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	50
Weight Per foot	0.83