



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LT5045 1/2" 45D LT Steel Conn *Crouse-Hinds*

|                  |   |
|------------------|---|
| Catalog Number   | LT5045  |
| Manufacturer     | Crouse-Hinds  |
| Description      | Liquid Tight 45°Connector, 1/2 In Trade Size, Malleable Iron (Body, Gland Nut);Steel (Ferrule, Lock Nut);Polyethylene (Sealing Ring);Thermoplastic Elastomer (Sealing Gasket) Material, Zinc Electroplated, 1.25 In Diameter, Non-Insulated, Threaded Connection, 27.1 LB/100 |
| Weight per unit  | 0.3200 (lbs/each)   |
| Product Category | Liquid Tight Fittings   |

### Features

|                   |                                   |
|-------------------|-----------------------------------|
| connection        | Threaded                          |
| dimensions        | 2.5000 IN X 1.2500 IN X 2.5000 IN |
| installation type | THREADED                          |

### Material, Color, and Finish

|       |                |
|-------|----------------|
| Color | MALLEABLE IRON |
|-------|----------------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 1/2" 45D LT STEEL CONN              |
| extra long description | MIDWEST LT5045 1/2 LT 45 DEGREE CON |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564450500 |
| UPC   | 784564450500   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | METALLIC FITTINGS     |
| Type                 | Liquidtight connector |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 25   |
| Weight Per each | 0.32 |

### Uses, Certifications, and Standards

|          |                             |
|----------|-----------------------------|
| standard | UL 467, UL 514B, CSA C22.11 |
|----------|-----------------------------|