



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ICN4P32SC35I 4-F32T8 120/277V Elec Bal

*Advance By Signify*

Catalog Number	ICN4P32SC35I
Manufacturer	Advance By Signify
Description	Electronic Ballast, High Frequency; Instant Start; Normal Output, HPF Circuit; F32T8, FBO31T8, F32T8/U6 Lamp; Straight/U Lamp; 4 Lamp(S); 32 W Lamp Wattage; Input Voltage 120/230/277 V; Input Current 0.94/0.49/0.41 Ampere; Input Power 112 W; 50/60 HZ
Weight per unit	1.2 (lbs/each)
Product Category	20010313162754

### Features

Ballast Factor	0.88 in
Circuit Type	NORMAL OUTPUT, HPF
Input Current	0.94/0.49/0.41 AMPERE
Input Power	112 W
Input Voltage	120/230/277 V
Lamp Style	STRAIGHT/U
Lamp Type	F32T8, FBO31T8, F32T8/U6
Lamp Wattage	32 W
Maximum THD	10 PERCENT
Minimum Starting Temperature	0 DEG F
Number of Lamps	798
Power Factor	0.99 in
Starting Type	INSTANT
Wiring	PARALLEL

### Dimensions and Weight

Size	9.5 INCH L X 1.7 INCH W X 1.18 INCH H
------	---------------------------------------

### Descriptions

Additional Information	USED ON LAMP F17T8, FBO16T8, F25T8, FBO24T8, F32T8/ES, F40T8; PACKAGING TYPE IC PACK
Commodity Description	Fluorescent Ballasts & Accy - Electronic
Description	4-F32T8 120/277V ELEC BAL
Long Description	ELECTRONIC BALLAST, HIGH FREQUENCY; INSTANT START; NORMAL OUTPUT, HPF CIRCUIT; F32T8, FBO31T8, F32T8/U6 LAMP; STRAIGHT/U LAMP; 4 LAMP(S); 32 W LAMP WATTAGE; INPUT VOLTAGE 120/230/277 V; INPUT CURRENT 0.94/0.49/0.41 AMPERE; INPUT POWER 112 W; 50/60 HZ
Product Type	Electronic Ballast



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Advance
GTIN	00781087106396
Manufacturers Part Number	ICN4P32SC35I
Model	ICN
UPC	781087106396

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	HIGH FREQUENCY

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	10
Weight Per each	1.15

## Uses, Certifications, and Standards

Approval	UL, CSA
Frequency Rating	50/60 Hz