

IEC Pin and Sleeve

Watertight Devices

Receptacle/Connector Replacement Interior

HUBBELL

Features

- Sequential contact engagement

Ordering Information

Description	UPC	Catalog Number
Pin and Sleeve Replacement Interior, For 3W 20A, IEC	783585420028	IN320BF

Device Color

Black



Standards

UL Listed
CSA Certified

Specifications

Gaskets	Neoprene
Hinge Spring	Stainless Steel
Contact Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel
Assembly Screws	Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC
Max Working Voltage 600V AC RM

Mechanical

Impact Resistance In accordance with UL746C
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount
Terminal Identification Terminals identified in accordance with North American and International conventions

Environmental

Flammability UL94-5VA and V-0 classification
Ingress Protection IP67 Suitability
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



IEC Pin and Sleeve

Watertight Devices

Receptacle/Connector Replacement Interior

HUBBELL

Features

- Sequential contact engagement

Ordering Information

Description	UPC	Catalog Number
Pin and Sleeve Replacement Interior, For 3W 20A, IEC	783585420028	IN320BF

Device Color

Black



Standards

UL Listed
CSA Certified

Specifications

Gaskets	Neoprene
Hinge Spring	Stainless Steel
Contact Carrier	High-Impact Thermoset
Terminal Screws	Stainless Steel
Assembly Screws	Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC
Max Working Voltage 600V AC RM

Mechanical

Impact Resistance In accordance with UL746C
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount
Terminal Identification Terminals identified in accordance with North American and International conventions

Environmental

Flammability UL94-5VA and V-0 classification
Ingress Protection IP67 Suitability
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

