

Eaton MMX12AA9D6N0-0

Catalog Number: MMX12AA9D6N0-0

Eaton M-Max Series sensorless vector adjustable frequency drive, Single-phase in, three-phase out, 9.6A, 3.0HP, 230V input and output voltage, FS3, W/O EMC



Photo is representative

General specifications

Product Name	Catalog Number
Eaton M-Max Series sensorless vector adjustable frequency drive	MMX12AA9D6N0-0
	UPC
	786685268620
Product Length/Depth	Product Height
11.5 in	5.5 in
Product Width	Product Weight
5.5 in	3.75 lb
Compliances	
CE Marked	
RoHS Compliant	
C-Tick Compliant	

Horsepower

3 hp

Phase

Single-phase in, three-phase out

Input voltage

230 V

Output voltage - max

230 V

Output voltage - min

230 V

Brochures

[Variable frequency drive - Product overview](#)

[M-Max Series adjustable frequency drives](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

Drawings

[MMX_\(FR3\) 3D Inventor](#)

[MMX_\(FR3\) 2D Drawing Xchange](#)

[MMX_\(FR3\) AutoCAD 2D Footprint](#)

[MMX_\(FR3\) AutoCAD 2D Footprint \(mm\)](#)

[MMX_\(FR3\) 2D PDF](#)

[MMX_\(FR3\) 3D Model Xchange](#)

Installation instructions

[User Manual, M-Max Series Adjustable Frequency Drive](#)

Specifications and datasheets

[Eaton Specification Sheet - MMX12AA9D6N0-0](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)