



ESSENTIAL SERIES

GENERAL PURPOSE LED BULBS

KT-LED13A19-O-8XX

REPLACEMENT LAMP

DESCRIPTION

13W A19 Lamp | 2700–5000K | >80 CRI | Omni-Directional



LAMP TYPE: A19
BASE TYPE: E26 (Medium)
WATTAGE: 13W
COLOR TEMPERATURE: 2700–5000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 3 Years
RATED LIFE: L70 (25,000 Hours)



TYPICAL APPLICATIONS

- Table, Desk, and Floor Lamps
- Wall Sconces
- Surface Mount Ceiling Fixtures
- General Lighting
- Pendant Lights

PRODUCT FEATURES

- Energy Efficient, 80%+ Energy Savings over Legacy Equivalents
- Lower Heat Generation than Legacy Equivalents
- PF >0.70
- Complies with Part 15 of FCC
- Durable Plastic housing lowers the risk for breakage
- ANSI compliant construction ensures fitment for intended applications
- Rated for open, recessed, and enclosed fixtures
- Operating temperature range –4°F/–20°C to 95°F/35°C
- Long Life minimizes replacement and maintenance costs
- Meets Energy Star requirements
- UL Listed
- Smooth diffused lens for comfortable glare free performance
- Smooth, uniform dimming
- Suitable for damp locations


ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED13A19-O-827	A19 bulb. Omni-Directional, dimmable	2700K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-O-830	A19 bulb. Omni-Directional, dimmable	3000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-O-835	A19 bulb. Omni-Directional, dimmable	3500K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-O-840	A19 bulb. Omni-Directional, dimmable	4000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W
KT-LED13A19-O-850	A19 bulb. Omni-Directional, dimmable	5000K	120V	13W	100W	E26	1600	>80	230°	Yes	123 lm/W

KT-LED13A19-O-8XX

REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	24.61" × 14.76" × 5.31"
Carton Weight	17.15 lbs

LAMP DIMENSIONS

A (Length)	4.57"
B (Diameter)	2.36"

BASE TYPE: E26 (Medium)

ORDERING INFORMATION

CATALOG NUMBER	CARTON QUANTITY	EASY CODE	UPC
KT-LED13A19-O-827	60 pcs	FWO-45	843654130248
KT-LED13A19-O-830	60 pcs	TGB-97	843654130255
KT-LED13A19-O-835	60 pcs	MAQ-54	843654130262
KT-LED13A19-O-840	60 pcs	RMC-77	843654130279
KT-LED13A19-O-850	60 pcs	JRR-45	843654130286

CATALOG NUMBER BREAKDOWN

KT-LED13A19-O-8XX

1 2 3 4 5 6 7

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature