

FEATURES & SPECIFICATIONS

INTENDED USE — Ideal for task lighting, restrooms, under/over cabinet, storage closets and displays. Certain airborne contaminants can diminish the integrity of acrylic and/or polycarbonate. [Click here for Acrylic-Polycarbonate Compatibility table for suitable uses.](#)

CONSTRUCTION — Lightweight compact-designed channel and cover are formed from cold-rolled steel and painted after fabrication.

Finish: High-gloss, baked white enamel (standard).

OPTICS — LEDs provide 88 color rendering index (CRI) at 4000 Kelvin with lumen output of 2,100 lumens. Diffuse acrylic lens providing a single smooth line of light shaped to resemble a fluorescent tube.

ELECTRICAL — 80% lumen maintenance at 60,000 hours; predicted life of more than 50,000 hours.

INSTALLATION — Snap-lock tool-less channel cover for quick and easy installation on ceiling or wall (horizontally or vertically). Not designed for continuous row mounting or daisy chaining.

LISTINGS — UL/C-UL listed to US and Canadian Safety Standards. For use in ambient temperatures from -22°F (-30°C) to 77°F (25°C). Approved FCC Part 15 Class B.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C.

Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select

LED Dry Location Striplight



Specifications

All dimensions are shown in inches (centimeters) unless otherwise noted.

LUMENS	LENGTH	WIDTH	DEPTH	WEIGHT	COMPARABLE LIGHT SOURCE
2100	46-1/2 (118.1)	1-1/2 (3.8)	2 (5.1)	3.96 lbs (1.8 kg)	1 - 32W T8

ORDERING INFORMATION

Catalog number	UPC	Description	Lumens	Wattage	Voltage	Color temperature	Pallet Quantity	Standard Carton Quantity
MNSL MV M6	7535739545437	LED dry location striplight	2100	24	120 - 277	4000K, 88 CRI	504	1

