

MPAP-200-MB-78



Catalog Number	MPAP-200-MB-78
Marketing Product Description	4 Terminal Ring Type Plain Top 1-200 Ampere Main Breaker Single Pedestal Direct Bury Parallel Wired
UPC	784572166400
Length (IN)	4
Width (IN)	8.156
Height (IN)	78
Brand Name	Milbank
Type	Ring Type Meter Socket
Application	Mobile Home Power
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	4L x 8.156W x 78H
Number Of Cutouts	1
Cutout Size	One 200 Ampere Main Breaker
Cable Entry	Underground
Terminal	Double Mechanical
Insulation	Fiberglass with Resin

Mounting	Pedestal
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	4 Terminal
Bypass Type	No Bypass
Number of Meter Positions	1 Position
Equipment Ground	Ground Bar
Hub Opening	Plain Top
Line Side Wire Range	6 AWG - 350 kcmil
Number Branch Circuits	4
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

MPAP-200-MB-78



Catalog Number	MPAP-200-MB-78
Marketing Product Description	4 Terminal Ring Type Plain Top 1-200 Ampere Main Breaker Single Pedestal Direct Bury Parallel Wired
UPC	784572166400
Length (IN)	4
Width (IN)	8.156
Height (IN)	78
Brand Name	Milbank
Type	Ring Type Meter Socket
Application	Mobile Home Power
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	4L x 8.156W x 78H
Number Of Cutouts	1
Cutout Size	One 200 Ampere Main Breaker
Cable Entry	Underground
Terminal	Double Mechanical
Insulation	Fiberglass with Resin

Mounting	Pedestal
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	4 Terminal
Bypass Type	No Bypass
Number of Meter Positions	1 Position
Equipment Ground	Ground Bar
Hub Opening	Plain Top
Line Side Wire Range	6 AWG - 350 kcmil
Number Branch Circuits	4
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.