



Shown actual size: Maestro® preset digital fade dimmer and 1-gang Satin Colors® wallplate in biscuit (BI)

## MAESTRO® digital fade dimmers

### product family features

- true multi-location dimming from each location
- tap on to favorite level; tap off; tap twice for full on
- touch rocker to adjust light level
- LEDs indicate light level and glow softly in the dark as a locator light
- delayed off provides light as you exit the room
- line frequency compensation maintains stable light
- coordinating Claro® and Satin Colors® wallplates available separately (including stainless steel)
- programming allows customized functions (application note #124 available at [www.lutron.com/applicationnotes](http://www.lutron.com/applicationnotes))
- eco-dim® model available

### available models

#### source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- electronic low-voltage lighting
- fluorescent lighting
- LED lighting
- quiet 7-speed fan controls
- quiet 7-speed fan/light controls
- exhaust fans (countdown timer only)

#### control locations

- single pole (one location)
- multi-location dimming (up to ten locations)

available colors (see pages 12-13 for color swatches)

#### colors (gloss finish)

<b>WH</b> white	<b>GR</b> gray
<b>IV</b> ivory	<b>BR</b> brown
<b>AL</b> almond	<b>BL</b> black
<b>LA</b> light almond	

#### colors (satin finish)

<b>HT</b> hot	<b>ES</b> eggshell
<b>MR</b> merlot	<b>BI</b> biscuit
<b>PL</b> plum	<b>GS</b> goldstone
<b>TQ</b> turquoise	<b>DS</b> desert stone
<b>TC</b> terracotta	<b>ST</b> stone
<b>GB</b> greenbriar	<b>LS</b> limestone
<b>BG</b> bluestone	<b>SW</b> snow
<b>MS</b> mocha stone	<b>PD</b> palladium
<b>SG</b> sea glass	<b>MN</b> midnight
<b>TP</b> taupe	<b>SI</b> sienna

#### colors & finishes key

- available in gloss finish
- available in satin finish
- available in all gloss and satin finishes

CAD file downloads available at [www.lutron.com/cad](http://www.lutron.com/cad)

Questions on installation or selection?  
Call Lutron® 24 hours/7 days a week at  
1.800.523.9466 or visit [www.lutron.com](http://www.lutron.com)

**digital switches**

**NEW**



- for multi-location switching, use one Maestro Wireless® multi-location switch with Maestro Wireless® companion switches

**incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, non-dim LED drivers, and general purpose fans\***

single pole/multi-location 6A light or 3A fan 120V	<b>MRF2-6ANS-</b>	<input type="checkbox"/>
single pole/multi-location 8A light or 5.8A fan 120V (spec grade)	<b>MRF2-8ANS-120-</b>	<input type="checkbox"/>

**incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, and non-dim LED drivers\***

single pole/multi-location 6A light 277V (spec grade)	<b>MRF2-6ANS-277-</b>	<input type="checkbox"/>
---	-----------------------	--------------------------

\* requires neutral wire connection

**companion switches**



- **for use with multi-location switches only** use up to nine Maestro® companion switches with one Maestro Wireless® multi-location switch
- can be used with multi-location timer switch
- no derating if ganged

**incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, non-dim LED drivers, and general purpose fans**

companion switch	120V	<b>MA-AS-</b>	<input type="checkbox"/>
companion switch	120V	<b>MSC-AS-</b>	<input type="checkbox"/>

**NEW**

companion switch	277V	<b>MA-AS-277-</b>	<input type="checkbox"/>
------------------	------	-------------------	--------------------------

Use standard single-pole and 3-way wiring for easy installation.

**See page 53 for available colors.**  
To order, add color suffix to model number.  
Example: **MRF2-6ANS-120- WH**

**colors & finishes key**

- available in gloss finish
- available in satin finish
- available in all gloss and satin finishes