



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LB55 1-1/2" Alu LB SR5 Cond Body

Crouse-Hinds

Catalog Number	LB55
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Body, Epoxy Powder Painted, 1-1/2 In Trade Size, Threaded/Set Screw Connection, 33.8 Cu.In Capacity, 90 ° Angle, 1-1/2 In Hub Size, 7.81 In Length, 2.49 In Width, 3.65 In Height, 0.98 LB/Ea
Weight per unit	0.9800 (lbs/each)
Product Category	Alum

Features

connection	Threaded / Set Screw
dimensions	7.8100 IN X 2.4900 IN X 3.6500 IN
Form	Series 5

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Height	3.65
Hub Size	1-1/2 in
Width	2.49

Descriptions

Description	1-1/2" ALU LB SR5 COND BODY
extra long description	MIDWEST LB55 1 1/2 RGD LB COND BODY
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer

Manufacturer Information

Brand	Eaton
GTIN	00784564140050
UPC	784564140050

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	2
Weight Per each	0.98

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting	Conduit
standard	UL, cUL