

# High Intensity Discharge Lamps

Page Updated 07 / 2010

| Bulb Shape   | Base      | LET | OP  | Watts | MOL (in) | LCL (in) | Order Code | Description       | ANSI Ballast Type | Case Qty | CBCP      | Rated Life (hrs) | Initial Lumens  | Mean Lumens     | Color Temp K | CRI | Additional Information           | Reduced Watts/ High Color Rendering | Footnotes  | Warning and Caution Notices |
|--|-----------|-----|-----|-------|----------|----------|------------|-------------------|-------------------|----------|-----------|------------------|-----------------|-----------------|--------------|-----|----------------------------------|-------------------------------------|------------|-----------------------------|
| <b>High Output and XHO Multi-Vapor® Metal Halide Lamps (continued)</b>         |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>250 Watts</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED28   | PosMog    | E   | HOR | 250   | 8.25     | 5.00     | 18101      | MVR250/HOR        | M58               | 12       |           | 15000            | 21000           | 10000           | 4200         | 65  | Clear, Position Oriented Socket  |                                     |            | 117                         |
|  |           | E   | HOR | 250   | 8.25     | 5.00     | 18103      | MVR250/C/HOR      | M58               | 12       |           | 15000            | 19700           | 9400            | 3600         | 70  | Coated, Position Oriented Socket |                                     |            | 117                         |
| <b>360 Watts - Watt-Miser® Energy-Saving Replacement for 400W Metal Halide</b> |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED37   | E39       | S   | VBU | 360   | 11.50    | 7.00     | 40053      | MVR360VBU/WM/XHO  | M59               | 6        |           | 20000            | 37000           | 24000           | 4200         | 65  | Extra High Output                | ↔                                   | 32, 49     | 121                         |
|  |           | S   | VBU | 360   | 11.50    | 7.00     | 40055      | MVR360C/VBUEWMXHO | M59               | 6        |           | 20000            | 35000           | 23000           | 4000         | 70  | Extra High Output                | ↔                                   | 32, 49     | 121                         |
| <b>400 Watts</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED37   | E39       | S   | VBU | 400   | 11.50    | 7.00     | 49657      | MVR400VBU/HO      | M59               | 6        |           | 20000            | 41000           | 26500           | 4000         | 65  | High Output                      |                                     | 49         | 121                         |
|  |           | S   | VBD | 400   | 11.50    | 7.00     | 49655      | MVR400/VBD        | M59               | 6        |           | 20000            | 41000           | 26500           | 4000         | 65  | Clear                            |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 20931      | MVR400SP30VBU/HO  | M59               | 6        |           | 20000            | 34000           | 20400           | 3200         | 70  | RE730 Phosphor Coating           |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 13923      | MVR400VBU/XHO     | M59               | 6        |           | 20000            | 43000           | 28000           | 4000         | 65  | Extra High Output                |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 13924      | MVR400C/VBU/XHO   | M59               | 6        |           | 20000            | 42000           | 27000           | 3700         | 70  | Extra High Output                |                                     | 49         | 121                         |
| ED28   | E39       | E   | VBU | 400   | 8.31     | 5.00     | 40335      | MVR400VBUED28HO   | M59               | 12       |           | 20000            | 41000           | 26500           | 4000         | 65  | Clear, Compact                   |                                     | 49         | 121                         |
| BT28   | E39       | E   | HOR | 400   | 8.25     | 5.00     | 40201      | MVR400/HOR/BT28   | M59               | 12       |           | 20000            | 37000           | 22000           | 4200         | 65  | Compact, Horizontal              |                                     | 49         | 117                         |
| BT37   | E39       | E   | HOR | 400   | 11.50    | 7.00     | 26218      | MVR400/HOR/MOG    | M59               | 6        |           | 20000            | 38000           | 22500           | 4200         | 65  | Clear                            |                                     | 49         | 117                         |
|  |           | E   | HOR | 400   | 11.50    | 7.00     | 26219      | MVR400C/HOR/MOG   | M59               | 6        |           | 20000            | 36800           | 22000           | 3900         | 70  | Coated                           |                                     | 49         | 117                         |
| <b>1000 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT56   | E39       | S   | VBU | 1000  | 15.37    | 9.50     | 44835      | MVR1000VBU/HO     | M47               | 6        |           | 15000            | 111000          | 87000           | 3800         | 65  | Clear                            |                                     | 49         | 121                         |
|  |           | S   | VBU | 1000  | 15.37    | 9.50     | 13137      | MVR1000C/VBU/HO   | M47               | 6        |           | 15000            | 107000          | 81500           | 3700         | 70  | Coated                           |                                     | 49         | 121                         |
| <b>Sports Lighting</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>1000 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| PAR64  | G38       | E   | U   | 1000  | 6.87     |          | 88514      | SPL1000/PAR64840  | HID               | 1        | 1,350,000 | 3500             | 63000           |                 | 4000         | 80  | Clear, Narrow Spot               |                                     | 38         | 124                         |
|  |           | E   | U   | 1000  | 6.87     |          | 88513      | SPL1000/PAR64/HR  | HID               | 1        | 1,350,000 | 3500             | 63000           |                 | 4000         | 80  | Clear, Narrow Spot               |                                     | 38         | 124                         |
| <b>1500 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| T7   | Rx7s      | E   | H   | 1500  | 10.12    | 5.00     | 16920      | SPL1500/H/652     | HID               | 1        |           | 6000             | 120000          | 90000           | 5200         | 65  | Frosted                          |                                     | 38         | 125                         |
| BT56   | E39       | E   | U   | 1500  | 15.37    | 9.50     | 47326      | MVR1500/U/SPORTS  | M48               | 6        |           | 3000             | 162000H/170000V | 137000H/153000V | 4000         | 65  | Clear                            |                                     | 17, 42, 49 | 117                         |
|  |           | E   | U   | 1500  | 15.37    | 9.50     | 37405      | MVR1500/HBU       | M48               | 6        |           | 3000             | 155000H/165000V | 134000H/140000V | 3900         | 65  | Clear                            |                                     | 16, 17, 49 | 117                         |
| <b>1650 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT56   | PosMog    | E   | HOR | 1650  | 15.37    | 9.50     | 25532      | MVR1650/HOR       | M112              | 6        |           | 3000             | 177000          | 145000          | 3200         | 65  | Clear, Position Oriented Socket  |                                     | 17, 49     | 117                         |
| <b>2000 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| T9   | #10 Spade | E   | HOR | 2000  | 10.00    | 4.30     | 12275      | MQI/2000/T9/40    | M134              | 10       |           | 3000             | 170000          | 153000          | 4000         | 65  | Clear                            |                                     |            | 125                         |
| <b>Protected Multi-Vapor® Metal Halide Lamps</b>                               |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>32 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | VBD | 32    | 5.43     | 3.43     | 12651      | MXR32C/VBD/O      | M100              | 6        |           | 10000            | 2400            | 1700            | 3200         | 70  | Coated, Protected                |                                     |            | 119                         |
|  |           | O   | VBU | 32    | 5.43     | 3.43     | 16469      | MXR32C/VBU/O      | M100              | 6        |           | 10000            | 2400            | 1700            | 3200         | 70  | Coated, Protected                |                                     |            | 119                         |
| <b>50 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 50    | 5.43     | 3.43     | 45670      | MXR50/U/MED/O     | M110              | 6        |           | 10000            | 3400            | 1700            | 3500         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 50    | 5.43     | 3.43     | 45671      | MXR50C/U/MED/O    | M110              | 6        |           | 10000            | 3200            | 1500            | 3500         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>70 Watts</b>  |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 70    | 5.43     | 3.43     | 12377      | MXR70/U/MED/O     | M98               | 6        |           | 12000            | 5500            | 3500            | 3200         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 70    | 5.43     | 3.43     | 12577      | MXR70C/U/MED/O    | M98               | 6        |           | 15000            | 5300            | 3300            | 3200         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>100 Watts</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 100   | 5.43     | 3.43     | 12381      | MXR100/U/MED/O    | M90               | 6        |           | 15000            | 9000            | 6200            | 3200         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 100   | 5.43     | 3.43     | 12579      | MXR100C/U/MED/O   | M90               | 6        |           | 15000            | 8500            | 5900            | 3200         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>150 Watts</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 150   | 5.43     | 3.43     | 45683      | MXR150/U/MED/O    | M102              | 6        |           | 15000            | 12500           | 8600            | 3500         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 150   | 5.43     | 3.43     | 45688      | MXR150C/U/MED/O   | M102              | 6        |           | 15000            | 12000           | 8300            | 3500         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>175 Watts</b>   |           |     |     |       |          |          |            |                   |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT28   | EX39      | O   | VBU | 175   | 8.25     | 5.00     | 49470      | MPR175VBU/O       | M57               | 6        |           | 10000            | 15700           | 8400            | 4000         | 65  | Clear, Protected, UV Control     |                                     |            | 119                         |
|  |           | O   | VBU | 175   | 8.25     | 5.00     | 11649      | MPR175C/VBU/O     | M57               | 6        |           | 10000            | 14300           | 7700            | 3800         | 70  | Coated, Protected, UV Control    |                                     |            | 119                         |
| ED28   | EX39      | O   | VBU | 175   | 8.25     | 5.00     | 61325      | MPR175VBU/PA/O    | M137              | 6        |           | 15000            | 16000           | 11000           | 3900         | 65  | Clear, Protected, UV Control     |                                     |            | 120                         |

# High Intensity Discharge Lamps

Page Updated 07 / 2010

| Bulb Shape   | Base      | LET | OP  | Watts | MOL (in) | LCL (in) | Order Code | Description      | ANSI Ballast Type | Case Qty | CBCP      | Rated Life (hrs) | Initial Lumens  | Mean Lumens     | Color Temp K | CRI | Additional Information           | Reduced Watts/ High Color Rendering | Footnotes  | Warning and Caution Notices |
|--|-----------|-----|-----|-------|----------|----------|------------|------------------|-------------------|----------|-----------|------------------|-----------------|-----------------|--------------|-----|----------------------------------|-------------------------------------|------------|-----------------------------|
| <b>High Output and XHO Multi-Vapor® Metal Halide Lamps (continued)</b>         |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>250 Watts</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED28   | PosMog    | E   | HOR | 250   | 8.25     | 5.00     | 18101      | MVR250/HOR       | M58               | 12       |           | 15000            | 21000           | 10000           | 4200         | 65  | Clear, Position Oriented Socket  |                                     |            | 117                         |
|  |           | E   | HOR | 250   | 8.25     | 5.00     | 18103      | MVR250/C/HOR     | M58               | 12       |           | 15000            | 19700           | 9400            | 3600         | 70  | Coated, Position Oriented Socket |                                     |            | 117                         |
| <b>360 Watts - Watt-Miser® Energy-Saving Replacement for 400W Metal Halide</b> |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED37   | E39       | S   | VBU | 360   | 11.50    | 7.00     | 40053      | MVR360VBU/WM/XHO | M59               | 6        |           | 20000            | 37000           | 24000           | 4200         | 65  | Extra High Output                | ↔                                   | 32, 49     | 121                         |
|  |           | S   | VBU | 360   | 11.50    | 7.00     | 40055      | MVR360C/VBUWMXHO | M59               | 6        |           | 20000            | 35000           | 23000           | 4000         | 70  | Extra High Output                | ↔                                   | 32, 49     | 121                         |
| <b>400 Watts</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED37   | E39       | S   | VBU | 400   | 11.50    | 7.00     | 49657      | MVR400VBU/HO     | M59               | 6        |           | 20000            | 41000           | 26500           | 4000         | 65  | High Output                      |                                     | 49         | 121                         |
|  |           | S   | VBD | 400   | 11.50    | 7.00     | 49655      | MVR400/VBD       | M59               | 6        |           | 20000            | 41000           | 26500           | 4000         | 65  | Clear                            |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 20931      | MVR400SP30VBU/HO | M59               | 6        |           | 20000            | 34000           | 20400           | 3200         | 70  | RE730 Phosphor Coating           |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 13923      | MVR400VBU/XHO    | M59               | 6        |           | 20000            | 43000           | 28000           | 4000         | 65  | Extra High Output                |                                     | 49         | 121                         |
|  |           | S   | VBU | 400   | 11.50    | 7.00     | 13924      | MVR400C/VBU/XHO  | M59               | 6        |           | 20000            | 42000           | 27000           | 3700         | 70  | Extra High Output                |                                     | 49         | 121                         |
| ED28   | E39       | E   | VBU | 400   | 8.31     | 5.00     | 40335      | MVR400VBUED28HO  | M59               | 12       |           | 20000            | 41000           | 26500           | 4000         | 65  | Clear, Compact                   |                                     | 49         | 121                         |
| BT28   | E39       | E   | HOR | 400   | 8.25     | 5.00     | 40201      | MVR400/HOR/BT28  | M59               | 12       |           | 20000            | 37000           | 22000           | 4200         | 65  | Compact, Horizontal              |                                     | 49         | 117                         |
| BT37   | E39       | E   | HOR | 400   | 11.50    | 7.00     | 26218      | MVR400/HOR/MOG   | M59               | 6        |           | 20000            | 38000           | 22500           | 4200         | 65  | Clear                            |                                     | 49         | 117                         |
|  |           | E   | HOR | 400   | 11.50    | 7.00     | 26219      | MVR400C/HOR/MOG  | M59               | 6        |           | 20000            | 36800           | 22000           | 3900         | 70  | Coated                           |                                     | 49         | 117                         |
| <b>1000 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT56   | E39       | S   | VBU | 1000  | 15.37    | 9.50     | 44835      | MVR1000VBU/HO    | M47               | 6        |           | 15000            | 111000          | 87000           | 3800         | 65  | Clear                            |                                     | 49         | 121                         |
|  |           | S   | VBU | 1000  | 15.37    | 9.50     | 13137      | MVR1000C/VBU/HO  | M47               | 6        |           | 15000            | 107000          | 81500           | 3700         | 70  | Coated                           |                                     | 49         | 121                         |
| <b>Sports Lighting</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>1000 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| PAR64  | G38       | E   | U   | 1000  | 6.87     |          | 88514      | SPL1000/PAR64840 | HID               | 1        | 1,350,000 | 3500             | 63000           |                 | 4000         | 80  | Clear, Narrow Spot               |                                     | 38         | 124                         |
|  |           | E   | U   | 1000  | 6.87     |          | 88513      | SPL1000/PAR64/HR | HID               | 1        | 1,350,000 | 3500             | 63000           |                 | 4000         | 80  | Clear, Narrow Spot               |                                     | 38         | 124                         |
| <b>1500 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| T7   | Rx7s      | E   | H   | 1500  | 10.12    | 5.00     | 16920      | SPL1500/H/652    | HID               | 1        |           | 6000             | 120000          | 90000           | 5200         | 65  | Frosted                          |                                     | 38         | 125                         |
| BT56   | E39       | E   | U   | 1500  | 15.37    | 9.50     | 47326      | MVR1500/U/SPORTS | M48               | 6        |           | 3000             | 162000H/170000V | 137000H/153000V | 4000         | 65  | Clear                            |                                     | 17, 42, 49 | 117                         |
|  |           | E   | U   | 1500  | 15.37    | 9.50     | 37405      | MVR1500/HBU      | M48               | 6        |           | 3000             | 155000H/165000V | 134000H/140000V | 3900         | 65  | Clear                            |                                     | 16, 17, 49 | 117                         |
| <b>1650 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT56   | PosMog    | E   | HOR | 1650  | 15.37    | 9.50     | 25532      | MVR1650/HOR      | M112              | 6        |           | 3000             | 177000          | 145000          | 3200         | 65  | Clear, Position Oriented Socket  |                                     | 17, 49     | 117                         |
| <b>2000 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| T9   | #10 Spade | E   | HOR | 2000  | 10.00    | 4.30     | 12275      | MQI/2000/T9/40   | M134              | 10       |           | 3000             | 170000          | 153000          | 4000         | 65  | Clear                            |                                     |            | 125                         |
| <b>Protected Multi-Vapor® Metal Halide Lamps</b>                               |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| <b>32 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | VBD | 32    | 5.43     | 3.43     | 12651      | MXR32C/VBD/O     | M100              | 6        |           | 10000            | 2400            | 1700            | 3200         | 70  | Coated, Protected                |                                     |            | 119                         |
|  |           | O   | VBU | 32    | 5.43     | 3.43     | 16469      | MXR32C/VBU/O     | M100              | 6        |           | 10000            | 2400            | 1700            | 3200         | 70  | Coated, Protected                |                                     |            | 119                         |
| <b>50 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 50    | 5.43     | 3.43     | 45670      | MXR50/U/MED/O    | M110              | 6        |           | 10000            | 3400            | 1700            | 3500         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 50    | 5.43     | 3.43     | 45671      | MXR50C/U/MED/O   | M110              | 6        |           | 10000            | 3200            | 1500            | 3500         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>70 Watts</b>  |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 70    | 5.43     | 3.43     | 12377      | MXR70/U/MED/O    | M98               | 6        |           | 12000            | 5500            | 3500            | 3200         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 70    | 5.43     | 3.43     | 12577      | MXR70C/U/MED/O   | M98               | 6        |           | 15000            | 5300            | 3300            | 3200         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>100 Watts</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 100   | 5.43     | 3.43     | 12381      | MXR100/U/MED/O   | M90               | 6        |           | 15000            | 9000            | 6200            | 3200         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 100   | 5.43     | 3.43     | 12579      | MXR100C/U/MED/O  | M90               | 6        |           | 15000            | 8500            | 5900            | 3200         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>150 Watts</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| ED17   | E26       | O   | U   | 150   | 5.43     | 3.43     | 45683      | MXR150/U/MED/O   | M102              | 6        |           | 15000            | 12500           | 8600            | 3500         | 70  | Clear, Protected                 |                                     |            | 120                         |
|  |           | O   | U   | 150   | 5.43     | 3.43     | 45688      | MXR150C/U/MED/O  | M102              | 6        |           | 15000            | 12000           | 8300            | 3500         | 70  | Coated, Protected                |                                     |            | 120                         |
| <b>175 Watts</b>   |           |     |     |       |          |          |            |                  |                   |          |           |                  |                 |                 |              |     |                                  |                                     |            |                             |
| BT28   | EX39      | O   | VBU | 175   | 8.25     | 5.00     | 49470      | MPR175VBU/O      | M57               | 6        |           | 10000            | 15700           | 8400            | 4000         | 65  | Clear, Protected, UV Control     |                                     |            | 119                         |
|  |           | O   | VBU | 175   | 8.25     | 5.00     | 11649      | MPR175C/VBU/O    | M57               | 6        |           | 10000            | 14300           | 7700            | 3800         | 70  | Coated, Protected, UV Control    |                                     |            | 119                         |
| ED28   | EX39      | O   | VBU | 175   | 8.25     | 5.00     | 61325      | MPR175VBU/PA/O   | M137              | 6        |           | 15000            | 16000           | 11000           | 3900         | 65  | Clear, Protected, UV Control     |                                     |            | 120                         |