

LED Replacement Lamps

LED PAR38 Indoor/Outdoor Commercial Directional Lamps



Project Name _____

Date _____ Type _____

Notes _____

For indoor and outdoor applications, Current's entire PAR38 portfolio offers a multitude of wattage options with a high light output. These range from standard to high light output.

PERFORMANCE HIGHLIGHTS:

PAR38 Lamps	
Light Output Range:	1050-3100 Lumens
CRI:	80-92
CCT:	2700K, 3000K, 3500K, 4000K & 5000K
Input Voltage:	120-277
Efficiency:	Up to 97 LPW
Wattage:	12W, 15W, 18W & 32W
Life:	25,000 hours L70
Temperature Rating:	-20°C to 45°C
Rating:	Damp & Wet

LIMITED WARRANTY

3 Years

FEATURES:

- Halogen-like color
- Available in different beam patterns
- These lamps are energy efficient, contain no lead or mercury

BENEFITS:

Energy + Cost Savings

- For example, using only 26 watts of energy, save over \$517 in energy costs over the rated life of the lamp versus a standard 120-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources
- Ideal for both indoor and outdoor applications
- UL wet rated for outdoor applications

LEARN MORE:

To learn more about saving money and energy, go to

www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED Replacement Lamps

LED PAR38 Indoor/Outdoor Commercial Directional Lamps

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Directional Lamps (PAR38)

Base Type	Order Type	Watts	Code	Description	Case Volts	MOL Qty**	Lumens (In)	Initial CRI	Color Temp	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	# Location Rating	Additional Information		
																Initial CBCP	
Compact PAR38 - Low Glare - Visual Comfort Lens™																	
PAR 38	E26	12	92971	LED12D38W3827/40	120	6	5.31	1050	2300	2700	81	100	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	92969	LED12D38W3827/25	120	6	5.31	1050	5500	2700	80	100	25,000	Yes	★	Damp	Narrow Flood, 25° beam
	E26	12	92972	LED12D38W3830/25	120	6	5.31	1050	5500	3000	81	100	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	92973	LED12D38WO3830/40	120	6	5.31	1050	2300	3000	80	100	25,000	Yes	★	Wet	Flood, 40° beam, White
	E26	12	24520	LED12D38W3930/12	120	6	5.31	950	15000	3000	90	90	25,000	-	-	Damp	Spot, 12° beam, White
	E26	12	93133599	LED12D38W3930/25	120	6	5.31	1050	4800	3000	90	100	25,000	Yes	-	Damp	Narrow Flood, 25° beam
	E26	18	92950	LED18D38OW3827/25	120	6	5.12	1550	5800	2700	81	120	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
	E26	18	92923	LED18D38W3927/25	120	6	5.31	1250	4900	2700	92	100	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	18	92958	LED18D38OW3827/40	120	6	5.12	1550	3800	2700	81	120	25,000	Yes	★	Wet	Flood, 40° beam, White
	E26	18	92926	LED18D38W3927/40	120	6	5.12	1250	2900	2700	92	120	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	18	92927	LED18D38W3930/15	120	6	5.32	1350	15000	3000	92	75	25,000	Yes	★	Wet	Spot, 15° beam, White
	E26	18	92961	LED18D38W3830/15	120	6	5.12	1750	20000	3000	81	150	25,000	Yes	★	Wet	Spot, 15° beam, White
	E26	18	93096546	LED18D38S3830/15	120	6	5.31	1750	20000	3000	80	150	25,000	Yes	-	Damp	Spot, 15° beam, Silver
	E26	18	65727	LED18D38OB3830/25	120	6	5.31	1550	6000	3000	80	150	25,000	Yes	★	Wet	Narrow Flood, 25° beam, Black
	E26	18	93096804	LED18D38OS3830/25	120	6	5.31	1550	6000	3000	80	150	25,000	Yes	-	Wet	Narrow Flood, 25° beam, Silver
	E26	18	92963	LED18D38OW3830/25	120	6	5.12	1550	6000	3000	81	120	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
	E26	18	92933	LED18D38W3930/25	120	6	5.31	1350	5200	3000	92	100	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	18	92967	LED18D38OW3830/40	120	6	5.12	1550	4000	3000	81	150	25,000	Yes	★	Wet	Flood, 40° beam, White
	E26	18	92934	LED18D38W3930/40	120	6	5.12	1350	3200	3000	92	120	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	18	85085	LED18D38OW3835/25	120	6	5.31	1700	6500	3500	81	120	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
E26	18	87917	LED18D38OW3835/40	120	6	5.31	1700	4400	3500	81	150	25,000	Yes	★	Wet	Flood, 40° beam, White	
E26	18	93171	LED18D38OW3840/25	120	6	5.31	1700	6500	4000	81	120	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
E26	18	93172	LED18D38OW3840/40	120	6	5.31	1700	4400	4000	81	150	25,000	Yes	★	Wet	Flood, 40° beam, White	
E26	18	65730	LED18D38OW3850/25	120	6	5.31	1700	6500	5000	81	120	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White	
E26	18	65731	LED18D38OW3850/40	120	6	5.31	1700	4400	5000	81	150	25,000	Yes	★	Wet	Flood, 40° beam, White	

Directional Lamps (PAR38 – High Output)

Single Optics																	
PAR 38	E26	32	75447	LED32DP38W830/15	120	6	5.12	3000	26,000	3000	82	250	25,000	Yes	★	Wet	Spot, 15° beam, White
	E26	32	88801	LED32DP38W830/25	120	6	5.12	3000	13,000	3000	80	250	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
	E26	32	88810	LED32DP38W830/40	120	6	5.12	3000	6,000	3000	80	250	25,000	Yes	★	Wet	Flood, 40° beam, White
	E26	32	30233	LED32DP38W835/15	120	6	5.12	3000	25,000	3000	80	250	25,000	Yes	★	Wet	Spot, 15° beam, White
	E26	32	30237	LED32DP38W835/25	120	6	5.12	3000	13,000	3000	80	250	25,000	Yes	★	Wet	Narrow Flood, 25° beam, White
	E26	32	30239	LED32DP38W835/40	120	6	5.12	3000	6,000	3000	80	250	25,000	Yes	★	Wet	Flood, 40° beam, White
	E26	32	20109	LED32P38W830/15	120-277	6	5.12	3000	25,000	3000	80	250	25,000	-	★	Wet	Spot, 15° beam, White
	E26	32	20130	LED32P38W830/25	120-277	6	5.12	3000	13,000	3000	80	250	25,000	-	★	Wet	Narrow Flood, 25° beam, White
	E26	32	20137	LED32P38W830/40	120-277	6	5.12	3000	6,000	3000	80	250	25,000	-	★	Wet	Flood, 40° beam, White

Directional Lamps (PAR38- Value)

Single Optics																	
PAR 38	E26	15	32213	LED15DP38W830/40	120	6	5.04	1300	2300	3000	81	90	25,000	Yes	★	Wet	Flood, 40° beam, White, STIR

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70) ** Minimum order quantity = 6 ★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.
Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/7TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.