



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NP0DMDXWH Low Voltage Multi Option Dimmer

*Lithonia Lighting*

Catalog Number	NP0DMDXWH
Manufacturer	Lithonia Lighting
Description	The Npodm DX Is A Single Gang Decorator Style Toggle and/or Dimming Wall Switch That Provides Control Of Lighting In A Space Featuring Soft-Click Buttons and The Ability to Adjust The Level Of Any Nlight Controlled Dimmable Lighting
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Dimmers

### Features

average life	87,600
dimmable	Yes
Hardware	Yes
Material	Plastic
Maximum Operating Temperature	60
Voltage Rating	Low Voltage
Warranty	5

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Height	5
Length	3.5
Width	2.5

### Descriptions

Description	LOW VOLTAGE MULTI OPTION DIMMER
extra long description	LITH NPODM DX WH Low Voltage Push-B
Long Description	The nPODM DX is a single gang decorator style toggle and/or dimming wall switch that provides control of lighting in a space featuring soft-click buttons and the ability to adjust the level of any nLight controlled dimmable lighting
Product Type	Switch

### Manufacturer Information

Brand	SENSOR SWITCH
GTIN	00745977903502
Manufacturers Part Number	NPODM DX WH
UPC	745977903502

### Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
----------------------	-----------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight	0.5
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Manufacturing, Offices & Banks, Retail, Sports and Recreation, Warehouses
environmental conditions	Indoor
Mounting	SURFACE
standard	C-UL-US, UL DLC Standard, ROHS