

DURACELL® PROCELL®

ALKALINE BATTERIES

DURACELL® PROCELL® alkaline batteries deliver outstanding performance and reliability. Major advantages are:

- long lasting and dependable – even after seven years of storage
- last up to ten times longer than super heavy duty zinc carbon batteries in power demanding applications
- long service life at high drain discharges
- operate reliably in temperature extremes of -20°C to 54°C
- date coded to ensure freshness
- economical bulk packaging for professional applications
- contain no added mercury



PC1300

SPECIFICATIONS	
Size/System:	Size D Alkaline
Voltage:	1.5
Max. Diameter:	1.346"
Max. Height:	2.421"
Average Weight:	4.86 oz (138.0g)
Maximum Volume:	3.44 in. ³ (56.4cm. ³)
Terminals:	Flat
Operating Temperature Range:	-4°F to 130°F (-20°C to 54°C)
Primary Usage:	Flashlights, Radios, Tape Recorders

PC1400

SPECIFICATIONS	
Size/System:	Size C Alkaline
Voltage:	1.5
Max. Diameter:	1.031"
Max. Height:	1.969"
Average Weight:	2.29 oz (65.0g)
Maximum Volume:	1.64 in. ³ (26.9cm. ³)
Terminals:	Flat
Operating Temperature Range:	-4°F to 130°F (-20°C to 54°C)
Primary Usage:	Flashlights, Radios, Tape Recorders



PC1500

SPECIFICATIONS	
Size/System:	Size AA Alkaline
Voltage:	1.5
Max. Diameter:	.571"
Max. Height:	1.988"
Average Weight:	0.83 oz (23.6g)
Maximum Volume:	0.51 in. ³ (8.4cm. ³)
Terminals:	Flat
Operating Temperature Range:	-4°F to 130°F (-20°C to 54°C)
Primary Usage:	Pagers, Remotes, Flashlights, Calculators

PC2400

SPECIFICATIONS	
Size/System:	Size AAA Alkaline
Voltage:	1.5
Max. Diameter:	.413"
Max. Height:	1.752"
Average Weight:	0.39 oz (11.0g)
Maximum Volume:	0.23 in. ³ (3.8cm. ³)
Terminals:	Flat
Operating Temperature Range:	-4°F to 130°F (-20°C to 54°C)
Primary Usage:	Pagers, Flashlights, TV Remotes

PC1604

SPECIFICATIONS	
Size/System:	9 Volt Alkaline
Voltage:	9.0
Max. Length:	.689"
Max. Width:	1.043"
Max. Height:	1.909"
Average Weight:	1.62 oz (45.9g)
Maximum Volume:	1.39 in. ³ (22.8cm. ³)
Terminals:	Miniature Snap
Operating Temperature Range:	-4°F to 130°F (-20°C to 54°C)
Primary Usage:	Infusion Pumps, Wireless Microphones, Smoke Alarms, Radios