

# Eaton PDG22G0020TFFL

Catalog Number: PDG22G0020TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Two Pole, 20A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X2T100)

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Power Defense molded case circuit breaker	PDG22G0020TFFL
	UPC
	786679945636
<b>Product Length/Depth</b>	<b>Product Height</b>
3.5 in	6 in
<b>Product Width</b>	<b>Product Weight</b>
2.75 in	3.75 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL 489
	CSA
	CCC Marked
	IEC 60947-2

## Delivery program

### Amperage Rating

20 A

### Circuit breaker frame type

Complete breaker

### Frame

2

### Number of poles

Two-pole

## General information

### Circuit breaker type

PD2 Global

### Class

Class A

### Trip Type

T298

## Technical data - Electrical

### Voltage rating

600 Vac

### Voltage rating - max

600 V

## Technical data - Mechanical - Terminals

### Terminals

Standard Terminals Load Only

## Technical information

### Interrupt rating

35 kAIC at 480 Vac

### Interrupt rating range

65 kAIC @240V (UL)

55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)

25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)

18 kAIC @600V (UL/CSA)

36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)

10 kAIC Icu @250 Vdc

20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)

10 kAIC Icu @125 Vdc

35 kAIC @480V (UL)

## Resources

### 3D CAD drawing package

[Eaton Power Defense PDG22G0020TFFL 3D drawing](#)

### Application notes

[Consulting application guide - molded case circuit breakers](#)

### Brochures

Power Defense technical selling booklet

Power Defense molded case circuit breaker selection poster

Power Defense brochure

### Brochures

Power Defense molded case circuit breakers - Frame 2 product aid

### Catalogs

Molded case circuit breakers catalog

### Certification reports

Power Defense Declaration concerning California's Proposition 65

PDG2 CB report

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG4 CCC certification

PDG4 CB report

### Installation instructions

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 2 pole instructions - IL012237EN H02

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01

Power Defense Frame 2 clamp terminal (steel), 20A, 2 pole instructions - IL012246EN H02

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 2 pole instructions - IL012238EN H02

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 box terminal (steel), 100A, 2 pole instructions - IL012234EN H02

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN

Power Defense Frame 2 screw terminal\_end cap kit, 225A, 2 pole instructions - IL012257EN H01

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 2 pole instructions - IL012236EN H02

Power Defense Frame 2 global terminal shield, 2 pole - IL012330EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions -

IL012278EN

Power Defense Frame 2 global interphase barrier 2 pole – IL012324EN

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K  
instructions- IL012239EN H01

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring  
instructions – IL012316EN

Power Defense Frame 2 locking devices and handle block instructions -  
IL012149EN

### Installation videos

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated  
Instructions.rh

Power Defense Frame 2 withTMTU, Shunt Trip\_UVR Animated  
Instructions.rh

### Multimedia

Power Defense Frame 5 Trip Unit How-To Video

Power Defense molded case circuit breakers

Eaton Power Defense for superior arc flash safety

Power Defense Breakers

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

Power Defense Frame 6 Trip Unit How-To Video

### Specifications and datasheets

Eaton Specification Sheet - PDG22G0020TFFL

### Time/current curves

Power Defense time current curve Frame 2 - PD2

### White papers

Molded case and low-voltage power circuit breaker health

Making a better machine

Single and double break MCCB performance revisited

Intelligent circuit protection yields space savings

Molded case and low-voltage breaker health

Safer by design: arc energy reduction techniques



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PDG22G0020TFFL

Catalog Number: PDG22G0020TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Two Pole, 20A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X2T100)

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Power Defense molded case circuit breaker	PDG22G0020TFFL
	UPC
	786679945636
<b>Product Length/Depth</b>	<b>Product Height</b>
3.5 in	6 in
<b>Product Width</b>	<b>Product Weight</b>
2.75 in	3.75 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	UL 489
	CSA
	CCC Marked
	IEC 60947-2

## Delivery program

### Amperage Rating

20 A

### Circuit breaker frame type

Complete breaker

### Frame

2

### Number of poles

Two-pole

## General information

### Circuit breaker type

PD2 Global

### Class

Class A

### Trip Type

T298

## Technical data - Electrical

### Voltage rating

600 Vac

### Voltage rating - max

600 V

## Technical data - Mechanical - Terminals

### Terminals

Standard Terminals Load Only

## Technical information

### Interrupt rating

35 kAIC at 480 Vac

### Interrupt rating range

65 kAIC @240V (UL)

55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)

25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)

18 kAIC @600V (UL/CSA)

36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)

10 kAIC Icu @250 Vdc

20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)

10 kAIC Icu @125 Vdc

35 kAIC @480V (UL)

## Resources

### 3D CAD drawing package

[Eaton Power Defense PDG22G0020TFFL 3D drawing](#)

### Application notes

[Consulting application guide - molded case circuit breakers](#)

### Brochures

Power Defense technical selling booklet

Power Defense molded case circuit breaker selection poster

Power Defense brochure

### Brochures

Power Defense molded case circuit breakers - Frame 2 product aid

### Catalogs

Molded case circuit breakers catalog

### Certification reports

Power Defense Declaration concerning California's Proposition 65

PDG2 CB report

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG4 CCC certification

PDG4 CB report

### Installation instructions

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 2 pole instructions - IL012237EN H02

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01

Power Defense Frame 2 clamp terminal (steel), 20A, 2 pole instructions - IL012246EN H02

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 2 pole instructions - IL012238EN H02

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 box terminal (steel), 100A, 2 pole instructions - IL012234EN H02

Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions - IL012106EN

Power Defense Frame 2 screw terminal\_end cap kit, 225A, 2 pole instructions - IL012257EN H01

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 2 pole instructions - IL012236EN H02

Power Defense Frame 2 global terminal shield, 2 pole - IL012330EN

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions -



IL012278EN

Power Defense Frame 2 global interphase barrier 2 pole – IL012324EN

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K  
instructions- IL012239EN H01

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring  
instructions – IL012316EN

Power Defense Frame 2 locking devices and handle block instructions -  
IL012149EN

### Installation videos

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated  
Instructions.rh

Power Defense Frame 2 withTMTU, Shunt Trip\_UVR Animated  
Instructions.rh

### Multimedia

Power Defense Frame 5 Trip Unit How-To Video

Power Defense molded case circuit breakers

Eaton Power Defense for superior arc flash safety

Power Defense Breakers

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism  
Installation How-To Video

Power Defense Frame 6 Trip Unit How-To Video

### Specifications and datasheets

Eaton Specification Sheet - PDG22G0020TFFL

### Time/current curves

Power Defense time current curve Frame 2 - PD2

### White papers

Molded case and low-voltage power circuit breaker health

Making a better machine

Single and double break MCCB performance revisited

Intelligent circuit protection yields space savings

Molded case and low-voltage breaker health

Safer by design: arc energy reduction techniques



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)