



PENE8, Oxide Inhibitor, 8 ounce

By Burndy
Catalog # [PENE8](#)

Oxide Inhibiting Electrical Joint Compound, 8 OZ, For Cu-Cu,
Cu Conduit Threads & Grounding Applications.



Application

Copper to copper applications

General

Application - For Use On	Copper to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-40 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	350 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592854
UPC 12 Digit	7818105928544
Viscosity at 100 Fahrenheit	250 °F

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	12
Container Size	8 oz
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

[3D Models - PENE8_MODEL-IGES](#)
[3D Models - PENE8_MODEL-PDF](#)
[3D Models - PENE8_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SC087710-01](#)
[SDS - PENETROX_E_Polish_GHS](#)
[SDS - PENETROX_E_ESPANOL_GHS](#)
[SDS - PENETROX_E_FRENCH_GHS](#)
[SDS - PENETROX_E_RUSSIAN_GHS](#)
[SDS - PENETROX_E_GHS](#)
[SDS - PENETROX_E_GERMAN_GHS](#)
[SDS - PENETROX_E_PORTUGUESE_GHS](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-PENE8-SPEC-EN | REV 8/2023