

# Eaton LR47

Catalog Number: LR47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1-1/4"

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>   | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | LR47                  |
|   | <b>UPC</b>            |
|   | 782274528809          |
| <b>Product Length/Depth</b>                                   | <b>Product Height</b> |
| 6.5 in  | 3.19 in               |
| <b>Product Width</b>  | <b>Product Weight</b> |
| 2.31 in   | 2.4 lb                |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

LR

### Trade size

1-1/4"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - LR47](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton LR47

Catalog Number: LR47

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, LR shape, 1-1/4"

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>   | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | LR47                  |
|   | <b>UPC</b>            |
|   | 782274528809          |
| <b>Product Length/Depth</b>                                   | <b>Product Height</b> |
| 6.5 in  | 3.19 in               |
| <b>Product Width</b>  | <b>Product Weight</b> |
| 2.31 in   | 2.4 lb                |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

12

## Product specifications

### Shape

LR

### Trade size

1-1/4"

### Material

Feraloy iron alloy

## Resources

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

### Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - LR47](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)