

**NEW!**  
more on  
reverse

# Rain-tight, Concrete-tight MC Cable Fittings

for PVC Jacketed MC Cable • LTMC50 Fits Cables 14/2 to 10/3



**Ideal for  
Parking Decks  
and High-rise  
Residential**

**One LTMC50  
fits 14/2 to 10/3 cable!**

Save time and money with Arlington's rain-tight, concrete-tight fittings designed especially for PVC jacketed MC cable – and Teck 90 cable.

The smallest size, 1/2" LTMC50, ships ready to install on #10, #12 or #14 PVC jacketed MC cable.




**NEW DESIGN**

LTMC50


Arlington's rain-tight, concrete-tight LTMC50 connector fits a range of cable sizes, so it reduces inventory, saving the cost of stocking several different fittings.

- Heavy-duty zinc diecast construction
- c UL us Listed


| CATALOG NUMBER           | UPC/DCI/NAED MFG #01 8997 | DESCRIPTION                                 | UNIT/STD PKG |
|--------------------------|---------------------------|---|--------------|
| LTMC50                   | 04279                     | Zinc Fitting for 1/2" PVC Jacketed MC Cable | 25 / 100     |
| MC Cable Range:          |                           | .415" to .565"                              |              |
| Teck Cable Range:        |                           | up to .580"                                 |              |
| Overall jacket OD Range: |                           | .550" to .670"                              |              |




LTMC50 Components




1 Remove sharp edges from cable end. Cut 1-1/4" off PVC jacket to prepare cable for fitting installation.



2 Push cable into fitting.



3 Cable installed. Tighten nut.



4 Install assembly in box.



Exploded view LTMC50 on cable

Patented/Other patents pending

Made in USA



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com


# Rain-tight, Concrete-tight MC Cable Fittings

for PVC Jacketed MC Cable, Teck cable • Fits Widest Cable Range

Our new larger rain-tight, concrete-tight MC cable fittings cover the widest cable ranges: 1/2 to 4/3.

They're compact - and the economical solution to installing PVC jacketed MC or Teck 90 cable.

• c UL us Listed



LTMC507

LTMC75



**Ideal for Parking Decks and High-rise Residential**

| CATALOG NUMBER                     | UPC/DCI/NAED MFG #01 8997 | DESCRIPTION            | UNIT/STD PKG |
|------------------------------------|---------------------------|------------------------|--------------|
| <b>LTMC507</b>                     | 16800                     | <b>1/2" trade size</b> | 25           |
| <b>MC Cable Range:</b>             |                           | .550" to .730"         |              |
| <b>Teck 90 Range:</b>              |                           | .580" to .765"         |              |
| <b>MC Cable Overall jacket OD:</b> |                           | .670" to .830"         |              |
| <b>Teck 90 Overall jacket OD:</b>  |                           | .670" to .855"         |              |

| CATALOG NUMBER                     | UPC/DCI/NAED MFG #01 8997 | DESCRIPTION            | UNIT/STD PKG |
|------------------------------------|---------------------------|------------------------|--------------|
| <b>LTMC75</b>                      | 16801                     | <b>3/4" trade size</b> | 25           |
| <b>MC Cable Range:</b>             |                           | .725" to .890"         |              |
| <b>Teck 90 Range:</b>              |                           | .765" to .980"         |              |
| <b>MC Cable Overall jacket OD:</b> |                           | .830" to .990"         |              |
| <b>Teck 90 Overall jacket OD:</b>  |                           | .855" to 1.06"         |              |

Patented/Other patents pending



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com

## Easy Installation!


**1** Cut PVC jacket back 1-1/4"



**2** Push jacketed cable into fitting



**3** Insert assembly into box



Distributed by

LTMC 0715/REV 0618 25M