

SELECTION CHART

Professional Series Multimeters

- Solid construction and rugged rubber boots.
- Data hold feature saves measurement for later viewing.

Additional Features for
Cat. Nos. MM1000, MM2000

- Bar graph responds quickly to changes in measurement.
- Max / Min / Relative reading for quick troubleshooting in the field.



Double Insulated



Measurement	MM100 Manual Ranging Multimeter	MM200 Auto Ranging Multimeter	MM1000 Electrician's / HVAC Multimeter	MM2000 Electrician's / HVAC TRMS Multimeter
AC Current	—	10A	10A	10A
DC Current	10A	10A	10A	10A
AC Voltage	600V	600V	1000V	1000V
DC Voltage	600V	600V	1000V	1000V
Resistance	2MΩ	40MΩ	40MΩ	40MΩ
Micro Amps	—	≥ 0.1μA	≥ 0.1μA	≥ 0.1μA
Capacitance	—	200μF	4000μF	4000μF
Temperature	—	-4 ~ 1832°F	-58 ~ 1832°F	-58 ~ 1832°F
Frequency / Duty Cycle	—	1MHz	1MHz	1MHz
Diode Test	●	●	●	●
Continuity	●	●	●	●
Battery Test	●	—	—	—
Features				
LCD Counts	2000	4000	4000	4000
Data Hold	●	●	●	●
Manual Range	●	—	●	●
Auto Range	—	●	●	●
Auto Power-Off	—	●	●	●
Backlight	—	●	●	●
Maximum / Minimum Hold	—	—	●	●
Relative Reading	—	—	●	●
Bar Graph	—	—	●	●
Magnetic Hanger Compatible	—	—	●	●
True RMS	—	—	—	●
Low Impedance	—	—	—	●

Listing



Cat. No.	CAT Rating	Batteries	Height	Width	Depth	Weight (oz.)	Included Accessories
MM100	CAT III 600V	1 x 9V	5.75" (146 mm)	2.75" (69.9 mm)	1.75" (44.5 mm)	8.0 (227 g)	test leads, battery
MM200	CAT III 600V	1 x 9V	5.75" (146 mm)	2.75" (69.9 mm)	1.75" (44.5 mm)	8.2 (232 g)	test leads, battery, thermocouple
MM1000	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (88.9 mm)	1.875" (47.6 mm)	14.0 (397 g)	test leads, batteries, thermocouple
MM2000	CAT IV 600V	2 x AAA	7.00" (178 mm)	3.50" (88.9 mm)	1.875" (47.6 mm)	14.0 (397 g)	test leads, batteries, thermocouple

Cat. No.	Type
69192	F 440mA / 1000V
69191	F 11A / 1000V



PROFESSIONAL SERIES MULTIMETERS

Auto Ranging Multimeter

MM 200

**Capacitance,
Temperature &
Frequency**



SPECIFICATION	MM200
AC Current	10A
DC Current	10A
AC Voltage	600V
DC Voltage	600V
Resistance	40MΩ
Micro Amps	≥ 0.1μA
Capacitance	200μF
Temperature	-4 ~ 1832°F
Frequency /Duty Cycle	1MHz
Diode Test	●
Continuity	●
Battery Test	—
CAT Rating	CAT III 600V
Listing	
Dimensions:	5.75" H x 2.75" W x 1.75" D (146 mm H x 69.9 mm W x 44.5 mm D)
Weight:	8.2 oz. (232 g)

Lighted Display

Auto Ranging
for ease of use

Double Insulated

10A AC/DC
Current



Temperature

Lead Storage
protects leads

Rubber
Molding
for drop
protection



Measure Circuit Breakers



Measure Temperature



Measure Frequency



Backlit Display

Designed by Electricians for Electricians