

Eaton PDG23G0100TFFL

Catalog Number: PDG23G0100TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 100A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

Photo is representative



General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Power Defense molded case circuit breaker | PDG23G0100TFFL |
| | UPC |
| | 786679912126 |
| Product Length/Depth | Product Height |
| 88.9 mm | 152.4 mm |
| Product Width | Product Weight |
| 104.6 mm | 1.82 kg |
| Warranty | Compliances |
| Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Certifications |
| | UL 489 |
| | IEC 60947-2 |
| | CCC Marked |
| | CSA |

Delivery program

Amperage Rating

100 A

Circuit breaker frame type

Complete breaker

Frame

2

Number of poles

Three-pole

General information

Circuit breaker type

PD2 Global

Class

Class A

Trip Type

T298

Technical data - Electrical

Voltage rating

600 Vac

Voltage rating - max

600 V

Technical data - Mechanical - Terminals

Terminals

Standard Terminals Load Only

Technical information

Interrupt rating

35 kAIC at 480 Vac

Interrupt rating range

55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

10 kAIC Icu @250 Vdc

65 kAIC @240V (UL)

25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC)

30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC)

36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC)

10 kAIC Icu @125 Vdc

8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC)

20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC)

18 kAIC @600V (UL/CSA)

35 kAIC @480V (UL)

Resources

3D CAD drawing package

[Eaton Power Defense PDG23G0100TFFL 3D drawing](#)

Application notes

[Consulting application guide - molded case circuit breakers](#)

Brochures

Power Defense brochure

Power Defense molded case circuit breaker selection poster

Power Defense technical selling booklet

Brochures

Power Defense molded case circuit breakers - Frame 2 product aid

Catalogs

Molded case circuit breakers catalog

Certification reports

PDG2 CB report

EU Declaration of Conformity - Power Defense molded case circuit breakers

PDG4 CCC certification

PDG4 CB report

Power Defense Declaration concerning California's Proposition 65

Installation instructions

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA150RF instructions - IL012244EN H01

Power Defense Frame 1 IEC and Frame 2 Rotary Mechanism with NFPA Handle Attachment Instructions (IL012260EN).pdf

Power Defense Frame 2 tunnel terminal (aluminum), 100A, 3 pole instructions - IL012237EN H03

Power Defense Frame 2 terminal kit - PDG2X3(2)(4)TA225RF instructions - IL012245EN H01

Power Defense Frame 2 screw terminal_end cap kit, 225A, 3 pole instructions - IL012258EN H01

Power Defense Frame 2 global terminal shield, 3 pole - IL012330EN

Power Defense Frame 2/3/4/5/6 voltage neutral sensor module wiring instructions - IL012316EN

Power Defense Frame 2 tunnel terminal (aluminum), 150A, 3 pole instructions - IL012238EN H03

Power Defense Frame 2 tunnel terminal kits - PDG2X1TA225K instructions- IL012239EN H01

Power Defense Frame 2 shunt trip UVR instructions - IL012130EN

Power Defense Frame 2 box terminal (aluminum), 225A, 3 pole instructions - IL012235EN H03

Power Defense Frame 2 tunnel terminal (aluminum), 50A, 3 pole instructions - IL012236EN H03

Power Defense Frame 1-2-3-4 IP door barrier assembly instructions - IL012278EN

Power Defense Frame 2 box terminal (steel), 100A, 3 pole instructions - IL012234EN H03

Power Defense Frame 2 multi wire connector kit -
PDG2X3(2)(4)TA2256W instructions - IL012242EN H01

Power Defense Frame 2 multi wire connector kit -
PDG2X3(2)(4)TA2253W instructions - IL012243EN H01

Power Defense Frame 2 Direct Rotary Handle Assy With Interlock
Version Instructions (IL012138EN).pdf

Power Defense Frame 2 handle mech direct rotary handle instructions -
IL012134EN

Power Defense Frame 2 handle mech variable depth rotary handle
instructions - IL012136EN

Power Defense Frame 2 PDG2 and PDC(E)9 breaker instructions -
IL012106EN

Power Defense Frame 2 clamp terminal (steel), 20A, 3 pole instructions
- IL012246EN H03

Power Defense Frame 2 locking devices and handle block instructions -
IL012149EN

Installation videos

Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle
Animated Instructions.rh

Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated
Instructions.rh

Power Defense Frame 2 Locking Devices and Handle Block Animated
Instructions.pdf.rh

Power Defense Frame 2 withTMTU, Shunt Trip_UVR Animated
Instructions.rh

Power Defense Frame 2 Bell Alarm with PXR Animated
Instructions.pdf.rh

Multimedia

Power Defense Frame 3 Variable Depth Rotary Handle Mechanism
Installation How-To Video

Power Defense Frame 2 Variable Depth Rotary Handle Mechanism
Installation How-To Video

Power Defense Frame 2 Direct Rotary Handle Mechanism Installation
How-To Video

Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To
Video

Eaton Power Defense for superior arc flash safety

Power Defense molded case circuit breakers

Power Defense Frame 6 Trip Unit How-To Video

Power Defense Frame 5 Trip Unit How-To Video

Power Defense Breakers

Specifications and datasheets

Eaton Specification Sheet - PDG23G0100TFFL

Time/current curves

Power Defense time current curve Frame 2 - PD2

White papers

Molded case and low-voltage power circuit breaker health

Making a better machine

Single and double break MCCB performance revisited

Intelligent circuit protection yields space savings

Molded case and low-voltage breaker health

Safer by design: arc energy reduction techniques



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia