

# Specifications



Photo is representative



## Eaton REN-20

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 20 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series REN fuse
<b>CATALOG NUMBER</b>	REN-20
<b>UPC</b>	051712100205
<b>EAN</b>	5027590098250
<b>PRODUCT LENGTH/DEPTH</b>	0.56 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	0.56 in
<b>PRODUCT WEIGHT</b>	0.41 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Not Applicable RoHS Compliant



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
VOLTAGE RATING	250 V

## General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

## Physical details

PACKAGING TYPE	Standard
----------------	----------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">REN-20~SUPER LAG RENEWABLE FUSE 20/250</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - REN-20</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.