



PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

Issue date: 02/18/2022

Revision date: 10/29/2025

Supersedes: 10/16/2025

Version: E

SECTION 1: Identification

1.1. Product identifier

Product form : Mixture
Product name : PENETROX™ A OXIDE INHIBITING COMPOUND

1.2. Other means of identification

No additional information available

1.3. Recommended use and restrictions on use

Use of the substance/mixture : General purpose corrosion inhibitor

1.4. Supplier

Burndy LLC
47 East Industrial Park Drive
Manchester, NH 03109 USA
(603) 647-5000

1.5. Emergency phone number

Emergency number : INFOTRAC: 1-800-535-5053 (U.S. & Canada) / 1-352-323-3500 (Outside the U.S. & Canada)

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS-US classification

Not classified

2.2. Label elements

GHS US labelling

No labelling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

2.5. Unknown acute toxicity

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%
Contains no hazardous ingredients at levels requiring disclosure by the OSHA Hazard Communication Standard (29 CFR 1910.1200)		

*In accordance with paragraph (i) of the OSHA Hazard Communication Standard (29 CFR §1910.1200), the specific chemical identity or exact weight % has been withheld as a trade secret.

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures general : If exposed or concerned, get medical attention/advice. Show this safety data sheet to the doctor in attendance. Wash contaminated clothing before re-use. Never give anything to an unconscious person.
First-aid measures after inhalation : IF INHALED: Remove to fresh air and keep at rest in a comfortable position for breathing.
First-aid measures after skin contact : IF ON SKIN (or clothing): Remove affected clothing and wash all exposed skin with water for at least 15 minutes.
First-aid measures after eye contact : IF IN EYES: Immediately flush with plenty of water for at least 15 minutes. Remove contact lenses if present and easy to do so. Continue rinsing.
First-aid measures after ingestion : IF SWALLOWED: rinse mouth thoroughly. Do not induce vomiting without advice from poison control center. Get medical attention if you feel unwell.

PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

4.2. Most important symptoms and effects (acute and delayed)

- Symptoms/effects : Not expected to present a significant hazard under anticipated conditions of normal use.
- Symptoms/effects after inhalation : Not expected to present a significant inhalation hazard under anticipated conditions of normal use.
- Symptoms/effects after skin contact : May cause skin irritation.
- Symptoms/effects after eye contact : Direct contact with eyes is likely to be irritating.
- Symptoms/effects after ingestion : May cause gastrointestinal irritation.

4.3. Immediate medical attention and special treatment, if necessary

No additional information available

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

- Suitable extinguishing media : Foam. Carbon dioxide. Dry powder.
- Unsuitable extinguishing media : Water jet.

5.2. Specific hazards arising from the chemical

- Fire hazard : Not flammable.
- Explosion hazard : Product is not explosive.
- Reactivity in case of fire : None known.

5.3. Special protective equipment and precautions for fire-fighters

- Precautionary measures fire : Eliminate all ignition sources if safe to do so.
- Firefighting instructions : Exercise caution when fighting any chemical fire. Use water spray or fog for cooling exposed containers. Do not dispose of fire-fighting water in the environment.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection. Self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Evacuate area. Ventilate area. Keep upwind. Spill should be handled by trained cleaning personnel properly equipped with respiratory and eye protection.

6.1.1. For non-emergency personnel

- Protective equipment : Wear Protective equipment as described in Section 8.
- Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

- Protective equipment : Wear suitable protective clothing, gloves and eye or face protection. Approved supplied-air respirator, in case of emergency.

6.2. Environmental precautions

Avoid release to the environment. Prevent entry to sewers and public waters.

6.3. Methods and material for containment and cleaning up

- For containment : Contain any spills with dikes or absorbents to prevent migration and entry into sewers or streams. Prevent entry to sewers and public waters.
- Methods for cleaning up : Shovel or sweep up and put in a closed container for disposal. Keep in suitable, closed containers for disposal. This material and its container must be disposed of in a safe way, and as per local legislation.

6.4. Reference to other sections

See Sections 8 and 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Do not handle until all safety precautions have been read and understood. Keep container closed when not in use. Avoid all eye and skin contact and do not breathe vapor and mist. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.
- Hygiene measures : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Wash contaminated clothing before reuse.

PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

7.2. Conditions for safe storage, including incompatibilities

- Storage conditions : Store in original container. Keep container closed when not in use. Containers which are opened should be properly resealed and kept upright to prevent leakage. Store in a dry, cool and well-ventilated place. Keep out of reach of children.
- Incompatible materials : Oxidizers.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Appropriate engineering controls

Appropriate engineering controls : Provide adequate general and local exhaust ventilation. Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Ensure adequate ventilation, especially in confined areas.

8.3. Individual protection measures, such as personal protective equipment

Personal protective equipment symbol(s):



Personal protective equipment:

Gloves. Protective goggles. [In case of inadequate ventilation] wear respiratory protection.

Hand protection:

Use gloves appropriate to the work environment. Gloves should be classified under Standard EN 374 or ASTM F1296.

Eye protection:

Use eye protection suitable to the environment. Avoid direct contact with eyes.

Skin and body protection:

Wear long sleeves, and chemically impervious PPE/coveralls to minimize bodily exposure.

Respiratory protection:

No respiratory protection needed under normal use conditions. Where excessive vapor, mist, or dust may result, use NIOSH approved respiratory protection equipment

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

- Physical state : Solid
- Appearance : Paste. Thick grease.
- Color : Gray
- Odor : Mild odor
- Odor threshold : No data available
- pH : No data available
- Melting point : No data available
- Freezing point : No data available
- Boiling point : No data available
- Flash point : > 204 °C (400 °F)
- Relative evaporation rate (butyl acetate=1) : No data available
- Flammability : No data available
- Vapor pressure : No data available
- Relative vapor density at 20°C : > 1 (air = 1)
- Relative density : 1.47
- Solubility : Insoluble in water
- Partition coefficient n-octanol/water (Log Pow) : No data available

PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

Auto-ignition temperature	: > 204 °C (400 °F)
Decomposition temperature	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive limits	: No data available
Oxidising properties	: No data available
Particle characteristics	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reactions known under normal conditions of use.

10.2. Chemical stability

Stable under recommended handling and storage conditions (see section 7).

10.3. Possibility of hazardous reactions

None under normal use.

10.4. Conditions to avoid

High temperatures, incompatible materials.

10.5. Incompatible materials

Oxidizers.

10.6. Hazardous decomposition products

Carbon oxides (CO, CO₂).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified
Symptoms/effects	: Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	: Not expected to present a significant inhalation hazard under anticipated conditions of normal use.
Symptoms/effects after skin contact	: May cause skin irritation.
Symptoms/effects after eye contact	: Direct contact with eyes is likely to be irritating.
Symptoms/effects after ingestion	: May cause gastrointestinal irritation.

SECTION 12: Ecological information

12.1. Ecotoxicity

Ecology - general	: Very toxic to aquatic life with long lasting effects.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

12.2. Persistence and degradability

No additional information available

PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

12.3. Bioaccumulative potential

No additional information available

12.4. Bioaccumulative potential

No additional information available

12.5. Other adverse effects

Other adverse effects : No data available.

Ozone : Not classified

Fluorinated greenhouse gases : No

SECTION 13: Disposal considerations

13.1. Disposal methods

Waste treatment methods : Do not discharge to public wastewater systems without permit of pollution control authorities. No discharge to surface waters is allowed without a permit.

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Do not allow the product to be released into the environment.

SECTION 14: Transport information

Department of Transportation (DOT)

In accordance with DOT

Not regulated for transport

Transport by sea (IMDG)

Transport document description (IMDG) : UN 3077 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (contains: Zinc), 9, III

UN-No. (IMDG) : 3077

Proper Shipping Name (IMDG) : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.

Class (IMDG) : 9 - Miscellaneous dangerous substances and articles

Packing group (IMDG) : III - substances presenting low danger

Limited quantities (IMDG) : 5 kg

Air transport (IATA)

Transport document description (IATA) : UN 3077 Environmentally hazardous substance, solid, n.o.s. (contains: Zinc), 9, III

UN-No. (IATA) : 3077

Proper Shipping Name (IATA) : Environmentally hazardous substance, solid, n.o.s.

Class (IATA) : 9 - Miscellaneous Dangerous Substances and Articles

Packing group (IATA) : III - Low danger

SECTION 15: Regulatory information

15.1. US Federal regulations

PENETROX™ A OXIDE INHIBITING COMPOUND

All chemical substances in this product are listed as "Active" in the EPA (Environmental Protection Agency) "TSCA Inventory Notification (Active-Inactive) Requirements Rule" ("the Final Rule") of Feb. 2019, as amended Feb. 2021, or are otherwise exempt or regulated by other agencies such as FDA or FIFRA

SARA Section 311/312 Hazard Classes	None
-------------------------------------	------

15.2. International regulations

No additional information available

15.3. US State regulations

This product does not contain any substances known to the state of California to cause cancer and/or reproductive harm

PENETROX™ A OXIDE INHIBITING COMPOUND

Safety Data Sheet

according to Federal Register / Vol. 89, No. 98 / Monday, May 20, 2024 / Rules and Regulations

Component	State or local regulations
Zinc (7440-66-6)	U.S. - Massachusetts - Right To Know List; U.S. - New Jersey - Right to Know Hazardous Substance List; U.S. - Pennsylvania - RTK (Right to Know) - Environmental Hazard List


SECTION 16: Other Information

Issue date : 2/18/2022
Revision date : 10/29/2025
Other information : Author: EMA.

NFPA health hazard : 0 - Materials that, under emergency conditions, would offer no hazard beyond that of ordinary combustible materials.

NFPA fire hazard : 0 - Materials that will not burn under typical fire conditions, including intrinsically noncombustible materials such as concrete, stone, and sand.

NFPA reactivity : 0 - Material that in themselves are normally stable, even under fire conditions.



HMIS Hazard Rating

Health : 0
Flammability : 0
Physical : 0

Indication of changes:

Revision 1.0: New SDS Created.
Revision 2.0. Modified composition/information on ingredients, transport information.
Revision 2.1. Modified composition.

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.